




CONCRETO EL

recessed wall light grey, 3.2W, 15lm, 3000K

A highly durable and striking design made from fashionable concrete: the rectangular CONCRETO EL wall-mounted light makes a strong statement in outdoor areas. The fixed LED emits a warm white light with 3000 Kelvin and offers an impressive service life of 50,000 hours. In addition, the grey concrete lamp has an IP65 protection class rating, which means it is ideally protected against dust and jets of water from all directions.



TECHNICAL DATA

Item no.	1006407
IP Code	IP 65
Impact resistance class	IK 03
Impact resistance	0.35 Joule
Assembly	Recessed
Assembly details	Wall
Primary nominal voltage	100-240V ~50/60Hz
Secondary power / voltage	700 mA
Safety class	I
Wattage	3.2 W
Minimum ambient temperature	-20 °C
Maximum ambient temperature	50 °C
Number of luminaires at LS B16A	28
Number of luminaires at LS C16A	48
Level of inrush current	15 A
Duration of inrush current	300 µs
Stroboscopic effect (SVM)	0
Lumen	15 lm
Colour temperature	3000 Kelvin
Color	grey
CRI	80
LXXBXX data	L80B50

Light Source

1319291	
---------	---

Service life	50000 h
Risk Group	1
Width	10 cm
Height	10 cm
Depth	7 cm
Net weight	0.52 kg
Gross weight	0.556 kg
Shape of cut-out	square
Installation length	9.2 cm
Installation width	9.2 cm
Installation depth	6.5 cm