



## TECHNICAL DATA

Item no.	1007142
Number of different light outlets	2
IP Code	IP 65
Impact resistance class	IK 08
Impact resistance	5 Joule
Assembly	Surface
Assembly details	Wall
Number of through-wires	74
Primary nominal voltage	220-240V ~50/60Hz
Secondary power / voltage	145 mA
Safety class	I
Wattage	5.7 W
Minimum ambient temperature	-20 °C
Maximum ambient temperature	45 °C
Operating efficiency (LOR)	0,72
Number of luminaires at LS B16A	74
Number of luminaires at LS C16A	123
Temperature at glass (light emission)	45 °C
Stroboscopic effect (SVM)	0.01
Lumen	560 lm
Colour temperature	2700/3000 Kelvin
Color	black

## Light Source



CRI	80
LXXBXX data	L70B50
Risk Group	1
Width	13.5 cm
Height	9 cm
Depth	3.1 cm
Net weight	0.47 kg
Gross weight	0.503 kg