



## TECHNICAL DATA

Item no.	1007201
IP Code	IP 44
Assembly	Surface
Assembly details	Wall
Dimmable	Yes
Dimming technology	Switch Dimmable
Primary nominal voltage	220-240V ~50/60Hz
Secondary power / voltage	24 V
Safety class	II
Wattage	25 W
Minimum ambient temperature	-15 °C
Maximum ambient temperature	40 °C
Stroboscopic effect (SVM)	0
Lumen	730 / 710 / 720 lm
Colour temperature	3000/4000/6500 Kelvin
Color	transparent
CRI	90
Risk Group	1
Depth	3.25 cm
Diameter	61 cm
Net weight	3.5 kg
Gross weight	3.745 kg

## Light Source

916520

