


LED Maschinenleuchte

LED machine luminaire




Maschinenleuchte CENALED SPOT Aufbau DC, Optik 65° für vollflächiges Licht

Artikel-Nr.: 121013-04
EAN: 4260556625737




Bestell-Nr.:	121013-04
Modell:	CENALED SPOT Aufbau
Bauform:	LED Aufbauleuchte
Leuchtmittel:	High Power LED
Lampenleistung:	~8,5 W
Lampenlichtstrom:	1120 lm
Lampenlichtausbeute:	134 lm/W
Lichtverteilung:	direkt
Lichtfarbe:	Neutralweiß (5000K)
Anschlusswert Leuchte:	24V DC ± 10%
Anschluss Leuchte:	M12 A-kodiert
Schutzart:	IP67
Schutzklasse:	III
Abstrahlwinkel:	65°
Betriebstemperatur:	-10... +50 °C
Farbwiedergabe (Ra):	> 80
Lampenlebensdauer:	> 60.000 h
Material Gehäuse:	Aluminium (pulverlackiert)
Material Abdeckung:	ESG 4 mm, sprungsicher
Höhe [B] x Breite [C]:	Raummaß: ~80 mm x 80 mm x 62,5 mm
Gewicht:	400 g
Bruttogewicht:	500 g
Risikogruppe (DIN EN 62471):	freie Gruppe
Kennzeichnung:	CE, UKCA, ETL Listed (5003526)
Befestigungszubehör:	Gelenkwinkel 214300-01 als Leuchtenhalter optional
Dimmbar:	optional über Zubehör
Gefertigt in:	Deutschland
Besonderheit:	65° Optik für vollflächiges Licht
Anmerkung:	Dichtung im Lieferumfang; Befestigung: rückseitig 3x Schrauben M6



Lampenlebensdauer in Betriebsstunden (L80/B10)

LED Maschinenleuchte
LED machine luminaire




Machine light CENALED SPOT Aufbau DC, (surface mounted light), optics 65°

Item number: 121013-04
EAN: 4260556625737



Order number:	121013-04
Model:	CENALED SPOT Aufbau
Type:	surface-mounted LED light
Illuminant:	High Power LED
Power consumption:	~8,5 W
Lamp luminous flux:	1120 lm
Lamp luminous efficiency:	134 lm/W
Light distribution:	direct
Light colour:	neutral white (5000K)
Connected load:	24V DC ± 10%
Connection (connector):	M12 A-coded
Degree of protection:	IP67
Class of protection:	III
Beam angle (optics):	65°
Operating temperature:	-10... +50 °C
Colour rendering (Ra):	> 80
Lamps lifetime:	> 60.000 h
Housing material:	aluminium (powder-coated)
Cover material:	safety glass 4 mm, crack-resistant
Height [B] x Width [C]:	cubic measure: ~80 mm x 80 mm x 62.5 mm
Weight (net):	400 g
Gross weight:	500 g
Risk group (DIN EN 62471):	free group
Marking:	CE, UKCA, ETL Listed (5003526)
Mounting accessories:	articulated joint 214300-01 as holder optional
Dimmable:	optional via accessories
Made in:	Germany
Feature:	65° optics for full flat light
Explanatory note:	seal included; mounting: 3x M6 screws at rear



Lamps lifetime in operation hours (L80/B10)