



## LEANLED II, 260 mm, opalweiÙe Abdeckung, kaskadierbar

|                     |               |
|---------------------|---------------|
| <b>Artikel-Nr.:</b> | 111010-32     |
| <b>EAN:</b>         | 4260556624228 |

|                               |   |
|-------------------------------|---|
| <b>Bestell-Nr.:</b>           | 111010-32   |
| <b>Modell:</b>                | LEANLED II  |
| <b>Bauform:</b>               | LED Aufbauleuchte   |
| <b>Leuchtmittel:</b>          | SMD LED   |
| <b>Lampenleistung:</b>        | ~6 W  |
| <b>Lampenlichtstrom:</b>      | 945 lm  |
| <b>Lampenlichtausbeute:</b>   | 145 lm/W  |
| <b>Lichtverteilung:</b>       | direkt  |
| <b>Lichtfarbe:</b>            | TageslichtweiÙ (5200 - 5700K)   |
| <b>Anschlusswert Leuchte:</b> | 24V DC $\pm$ 10%  |
| <b>Anschluss Leuchte:</b>     | M12 A-kodiert   |
| <b>Schutzart:</b>             | IP54  |
| <b>Schutzklasse:</b>          | III   |
| <b>Entblendung:</b>           | opalweiÙ  |
| <b>Abstrahlwinkel:</b>        | 120°  |
| <b>Betriebstemperatur:</b>    | -10... +60 °C   |
| <b>Farbwiedergabe (Ra):</b>   | > 85  |
| <b>Lampenlebensdauer:</b>     | > 60.000 h  |
| <b>Material GehäÙe:</b>       | Aluminium   |
| <b>Material Abdeckung:</b>    | Polycarbonat, matt  |
| <b>HöÙe [B] x Breite [C]:</b> | 31 mm x 26 mm   |
| <b>Länge [A]:</b>             | 260 mm  |
| <b>Gewicht:</b>               | 200 g   |
| <b>Bruttogewicht:</b>         | 350 g   |
| <b>Risikogruppe:</b>          | freie Gruppe  |
| <b>Kennzeichnung:</b>         | CE, ETL Listed  |
| <b>BefestigungszubehöÙr:</b>  | 2 Paar Halterungen (drehbare oder planare Befestigung) im Lieferumfang        |
| <b>Dimmbar:</b>               | optional über ZubehöÙ   |
| <b>Gefertigt in:</b>          | Deutschland   |
| <b>Besonderheit:</b>          | kaskadierbar, mehrere Leuchten lassen sich bis max. 4A elektrisch verketteten |



Lampenlebensdauer in Betriebsstunden (L80/B10)



## LEANLED II, 260 mm, opal white cover, cascadable

**Item number:** 111010-32  
**EAN:** 4260556624228

|                                   |  |
|-----------------------------------|--|
| <b>Order number:</b>              | 111010-32  |
| <b>Model:</b>                     | LEANLED II   |
| <b>Type:</b>                      | LED surface-mounted luminaire  |
| <b>Illuminant:</b>                | SMD LED  |
| <b>Power consumption:</b>         | ~6 W   |
| <b>Lamp luminous flux:</b>        | 945 lm   |
| <b>Lamp luminous efficiency:</b>  | 145 lm/W   |
| <b>Light distribution:</b>        | direct   |
| <b>Light colour:</b>              | daylight white (5200 - 5700K)  |
| <b>Connected load:</b>            | 24V DC $\pm$ 10%   |
| <b>Connection (connector):</b>    | M12 A-type encoded   |
| <b>Degree of protection:</b>      | IP54   |
| <b>Class of protection:</b>       | III  |
| <b>Glare-free</b>                 | opal white   |
| <b>Beam angle (optics):</b>       | 120°   |
| <b>Operating temperature:</b>     | -10... +60 °C  |
| <b>Colour rendering (Ra):</b>     | > 85   |
| <b>Lamps lifetime:</b>            | > 60,000 h   |
| <b>Housing material:</b>          | aluminium  |
| <b>Cover material:</b>            | Polycarbonate, soft  |
| <b>Height [B] x Width [C]:</b>    | 31 mm x 26 mm  |
| <b>Length [A]:</b>                | 260 mm   |
| <b>Weight (net):</b>              | 200 g  |
| <b>Gross weight:</b>              | 350 g  |
| <b>Risk group (DIN EN 62471):</b> | free group   |
| <b>Marking:</b>                   | CE, ETL Listed   |
| <b>Mounting accessories:</b>      | 2 pairs mounting holders (holder for swivel or planar mounting) in delivery scope                                  |
| <b>Dimmable:</b>                  | via optional accessory   |
| <b>Made in:</b>                   | Germany  |
| <b>Feature:</b>                   | cascadable, several luminaires can be interlinked electrically. The entire power consumption may not exceed 4A DC. |



Lamps lifetime in operation hours (L80/B10)