



LEANLED II, 760 mm, opalweiße Abdeckung, kaskadierbar

Artikel-Nr.:	111010-35
EAN:	4260556624259

Bestell-Nr.:	111010-35
Modell:	LEANLED II
Bauform:	LED Aufbauleuchte
Leuchtmittel:	SMD LED
Lampenleistung:	~19 W
Lampenlichtstrom:	2835 lm
Lampenlichtausbeute:	145 lm/W
Lichtverteilung:	direkt
Lichtfarbe:	Tageslichtweiß (5200 - 5700K)
Anschlusswert Leuchte:	24V DC ± 10%
Anschluss Leuchte:	M12 A-kodiert
Schutzart:	IP54
Schutzklasse:	III
Entblendung:	opalweiß
Abstrahlwinkel:	120°
Betriebstemperatur:	-10... +60 °C
Farbwiedergabe (Ra):	> 85
Lampenlebensdauer:	> 60.000 h
Material Gehäuse:	Aluminium
Material Abdeckung:	Polycarbonat, matt
Höhe [B] x Breite [C]:	31 mm x 26 mm
Länge [A]:	760 mm
Gewicht:	500 g
Bruttogewicht:	800 g
Risikogruppe:	freie Gruppe
Kennzeichnung:	CE, ETL Listed
Befestigungszubehör:	2 Paar Halterungen (drehbare oder planare Befestigung) im Lieferumfang
Dimmbar:	optional über Zubehör
Gefertigt in:	Deutschland
Besonderheit:	kaskadierbar, mehrere Leuchten lassen sich bis max. 4A elektrisch verketteten



Lampenlebensdauer in Betriebsstunden (L80/B10)



LEANLED II, 760 mm, opal white cover, cascadable

Item number:	111010-35
EAN:	4260556624259

Order number:	111010-35
Model:	LEANLED II
Type:	LED surface-mounted luminaire
Illuminant:	SMD LED
Power consumption:	~19 W
Lamp luminous flux:	2835 lm
Lamp luminous efficiency:	145 lm/W
Light distribution:	direct
Light colour:	daylight white (5200 - 5700K)
Connected load:	24V DC $\pm$ 10%
Connection (connector):	M12 A-type encoded
Degree of protection:	IP54
Class of protection:	III
Glare-free	opal white
Beam angle (optics):	120°
Operating temperature:	-10... +60 °C
Colour rendering (Ra):	> 85
Lamps lifetime:	> 60,000 h
Housing material:	aluminium
Cover material:	Polycarbonate, soft
Height [B] x Width [C]:	31 mm x 26 mm
Length [A]:	760 mm
Weight (net):	500 g
Gross weight:	800 g
Risk group (DIN EN 62471):	free group
Marking:	CE, ETL Listed
Mounting accessories:	2 pairs mounting holders (holder for swivel or planar mounting) in delivery scope
Dimmable:	via optional accessory
Made in:	Germany
Feature:	cascadable, several luminaires can be interlinked electrically. The entire power consumption may not exceed 4A DC.



Lamps lifetime in operation hours (L80/B10)