

# AQUAPIX®

## WDV5630

WATER  
PROOF

DV CAMCORDER



**4K** 5 METERS  
WATER  
PROOF

**5M**  
WATERPROOF

**13MP**  
SENSOR

**56MP**  
MAX.  
RESOLUTION

**18X**  
DIGITAL  
ZOOM

**3.0"**  
7.6CM IPS  
DISPLAY

**4K**  
VIDEO

**ISO  
1600**

**MICRO**  
SD CARDS  
UP TO 128GB

**LITHIUM  
BATTERY**

### WDV5630 CAMCORDER

WDV5630 GREYBLUE	WDV5630 YELLOW
Art. Nr. 24010	Art. Nr. 24013
EAN 4260041686397	EAN 4260041686403

### WATERPROOF

Waterproof housing	Up to 5m
--------------------	----------

### RESOLUTIONS

Video	4K 30fps
	2.7K 30fps
	1080P 60fps/30fps
	720P 60fps/30fps
Photo	5M, 8M, 12M, 16M*, 20M*, 24M*, 30M*, 48M*, 56M*

### DISPLAY

LCD Display	3.0"/7.6cm
-------------	------------

### FEATURES

Sensor	13MP
Digital Zoom	18x
Lens	F/2.6 f=7.0mm
Focus Range	1.0m ~ infinity
Exposure	-3.0EV - +3.0EV
Loop Recording	Yes
Time Lapse	Yes
White Balance	Auto / Sunny / Cloudy / Fluorescent / Tungsten
ISO	Auto / 100 / 200 / 400 / 800 / 1600
File Format	MP4, JPEG
Self-Timer	2 sec / 5 sec / 10 sec
Auto Power Off	1 min / 2 min / 3 min / 5 min / 10 min
Webcam Function	For Windows only
Interface	USB 2.0 Micro, HDMI
Power Source	3400mAh 3.8V 12.92Wh Lithium battery
Dimensions	135 x 65 x 60mm, 370g (incl. battery)

### EXTERNAL MEMORY

(Not included)
Compatible with microSD cards up to max. 128GB

### INCLUDED

Camcorder, Pouch, Lithium Battery, USB Cable, HDMI Cable, User Manual



\*by interpolation



← 135 mm →

