

AQUAPIX®

W2024 SPLASH



3 METERS
WATER
PROOF



3M
WATERPROOF

16MP
MAX.
RESOLUTION

8X
DIGITAL
ZOOM

2.4"
6.1CM
DISPLAY

HD
VIDEO

VIDEO
RECORDING
WITH SOUND

MICRO
SD CARDS
UP TO 32GB

ISO
400

4
COLOUR
EFFECTS

W2024 SPLASH

W2024-I Iceblue	W2024-Y Yellow	W2024-P Pink	W2024-O Orange
Art. Nr. 10065	Art. Nr. 10067	Art. Nr. 10066	Art. Nr. 10068
EAN 4260041686175	EAN 4260041686199	EAN 4260041686182	EAN 4260041686427

WATERPROOF CAMERA

Waterproof housing Up to 3m

RESOLUTIONS

Photo	16M* / 14M* / 12M* / 10M* / 8M* / 7M* / 5M / 3M / 2M / VGA
Video	1280x720p, 640x480p, 320x240p

DISPLAY

LCD display 2.4"/6.1cm

FEATURES

Sensor	5MP
Digital zoom	8x
Lens	F/2.8, f=6.8mm
Focus range	1m ~ infinity
Exposure	-3.0EV - +3.0EV
Image Quality	Normal / Fine / Super Fine
Anti shake functon	Yes
Face detection	Yes
Scene mode	Auto, Scenery, Portrait, Night Scenery, Night Portrait, High Sensitivity, Beach
Colour effects	Standard, Sepia, Monochrome, Vivid
Flash mode	Off, On, Auto, Red Eye Reduction
White balance	Auto / Daylight / Cloudy / Fluorescent / Tungsten
ISO	Auto / 100 / 200 / 400
File format	JPEG, AVI
Self-timer	2 sec / 5 sec / 10 sec
Auto Power Off	1 min / 3 min / 5 min / 10 min
Interface	USB 2.0 Micro
Power source	2xAAA battery (not included)
Dimensions	92 x 64 x 29 mm, 97g (without batteries)

EXTERNAL MEMORY

(not included)
Compatible with microSD cards up to max. 32GB

INCLUDED

Hand strap, manual, usb cable

*by interpolation

