

# AQUAPIX®

## W3048 EDGE



3 METERS  
WATER  
PROOF

4K  
VIDEO

DUAL  
DISPLAY  
for SELFIES



3M  
WATERPROOF

13MP  
SENSOR

48MP  
MAX.  
RESOLUTION

16X  
DIGITAL  
ZOOM

3.0"  
7.6CM BACK  
DISPLAY

2.0"  
5CM FRONT  
DISPLAY

4K  
VIDEO

ISO  
400

MICRO  
SD CARDS  
UP TO 128GB

LITHIUM  
BATTERY  
EXCHANGEABLE

### W3048 EDGE

W3048-Y Yellow	W3048-I Iceblue	W3048-V Violet
Art. Nr. 10076	Art. Nr. 10075	Art. Nr. 10074
EAN 4260041686106	EAN 4260041686090	EAN 4260041686434

### WATERPROOF

Waterproof housing Up to 3m

### RESOLUTIONS

Photo	48M* / 30M* / 24M* / 20M* / 16M* 12M / 8M / 7MHD / 5M / 3M / 2MHD
Video	4K* 3840x2160 10fps / 2.7K* 2688x1520p 25fps FHD 1920x1080p / HD 1280x720p

### DUAL DISPLAY

Front display	2.0"/5.0cm (4:3)
Main display	3.0"/7.6cm (16:9)

### FEATURES

Sensor	13MP
Digital zoom	16x
Lens	F/2.2 f=2.0mm
Focus range	1.5m ~ infinity
Exposure	-3.0EV - +3.0EV
Face detection	Yes
Anti shake functon	Yes
Flash mode	Off, On, Auto
White balance	Auto / Daylight / Cloudy / Fluorescent / Tungsten
Scenes	Auto / Scenery / Portrait / Night scenery / Night portrait / High sensivity / Sport / Beach /Party
ISO	Auto / 100 / 200 / 400
File format	JPEG, AVI
Self-timer	2 sec / 5 sec / 10 sec
Auto Power Off	1 min / 3 min / 5 min
Interface	Micro USB
Power source	1500mAh lithium battery (exchangeable)
Dimensions	110 x 68 x 32mm, 138g (without battery)

**EXTERNAL MEMORY** (not included)  
Compatible with microSD cards up to max. 128GB

### INCLUDED

Pouch, hand strap, lithium battery, usb cable, manual

\*by interpolation



**2.0"** FRONT DISPLAY

110 mm



**3.0"** BACK DISPLAY

68 mm

