

AQUAPIX®

W3027 wave



3 METERS
WATER
PROOF

Full HD
1920x1080

3M
WATERPROOF

5MP
SENSOR

30MP
MAX.
RESOLUTION

4X
DIGITAL
ZOOM

2.7"
6.8CM
DISPLAY

FULL HD
VIDEO

MICRO
SD CARDS
UP TO 128GB

ISO
400

LITHIUM
BATTERY
EXCHANGEABLE

W3027 WAVE

W3027 Marine Blue	W3027 Sunset Orange	
Art. Nr. 10034	Art. Nr. 10031	
EAN 4260041686458	EAN 4260041686441	

WATERPROOF CAMERA

Waterproof housing Up to 3m

RESOLUTIONS

Photo	30M* / 24M* / 20M* / 16M* / 12M* / 8M* / 7MHD* / 5M / 3M / 2MHD
Video	FHD 1920x1080, HD 1280x720, VGA 640x480

DISPLAY

LCD display 2.7"/6.8cm

FEATURES

Sensor	5MP
Digital zoom	4x
Lens	F/3.0 f=8.15mm
Focus range	1m ~ infinity
Exposure	-3.0EV - +3.0EV
Image Quality	Normal / Fine / Super Fine
Anti shake function	Yes
Face detection	Yes
Scene mode	Auto, Scenery, Portrait, Night Scenery, Night Portrait, High Sensitivity, Sport, Beach, Party
Colour effects	Standard, Sepia, Monochrome, Vivid
Flash mode	Off, On, Auto, Red Eye Reduction
White balance	Auto / Daylight / Cloudy / Fluorescent / Incandescent
ISO	Auto / 100 / 200 / 400
File format	JPEG, AVI
Self-timer	2 sec / 5 sec / 10 sec
Auto Power Off	1 min / 3 min / 5 min
Interface	USB 2.0 Micro
Power source	650mAh lithium battery (exchangeable)
Dimensions	105 x 63 x 24 mm, 130g

EXTERNAL MEMORY

(not included)
Compatible with microSD cards up to max. 128GB

INCLUDED

Pouch, hand strap, lithium battery, usb cable, manual

*by interpolation

