




## Exchangeable plugs Utskiftbare plugger



Connecting the exchangeable plugs is a snap! All plugs have a snap-lock for added safety. Both plug ends are clearly marked to connect desired polarity.

Å sette på en utskiftbar plugg er enkelt. Alle pluggene har en hakelås for sikkerhets skyld. Begge ender er tydelig merket for å koble til ønsket polaritet.

### EIAJ RC5320A Plugs



Art. no. 131125

#### 53201

- L: 9,5
- Dy: 2,35
- Di: 0,7

Class I



Art. no. 131126

#### 53202

- L: 9,5
- Dy: 4
- Di: 1,7

Class II



Art. no. 131127

#### 53203

- L: 9,5
- Dy: 4,75
- Di: 1,7

Class III



Art. no. 131128

#### 53204

- L: 9,5
- Dy: 5,5
- Di: 3,3

• Dp: 1,0  
Class IV

Push on terminals / Kabelsko  
Type 131341



Art. no. 131123

#### 3615

- L: 14,5
- Dy: 3,5



Art. no. 131120

#### 3617

- L: 12
- Dy: 5,5
- Di: 2,5



Art. no. 131193

#### 3618

- L: 9,5 • Dy: 5,5
- Di: 2,45



Art. no. 131124

#### 3620

- L: 11,5
- Dy: 2,5



Art. no. 131122

#### 3627

- L: 14 • Dy1: 5
- Dy2: 6,2
- Di: 1,97



Art. no. 131119

#### 3630

- L: 12
- Dy: 5,5
- Di: 2,1



Art. no. 131192

#### 3630A

- L: 12
- Dy: 5,5
- Di: 2,1



Art. no. 131121

#### 3635

- L: 9
- Dy: 3,8
- Di: 1,3



## Exchangable plug packs Poser m. utskiftbare plugger

Pack / pose 1: Type 9000-200

All 36-series plugs (8 pcs)

Alle 36-serie pluggene (8 stk)

Pack / pose 2: Type 9000-201

All EIAJ plugs (4 pcs)

Alle EIAJ pluggene (4 stk)

Pack / pose 3: Type 9000-202

1x all plugs (12 pcs)

1x alle plugger (12 stk)

