

2USB easyCharge DUO USB AC 18.0W/3.6A Matt Black



General Information

Name:	2USB easyCharge DUO USB AC 18.0W/3.6A Matt Black
SKU:	2U-449719

Basics

Brand:	2USB
Model Number:	JP-9012F
EAN:	8718868449719
Customs Number (HS-Code):	8536.69.90.99
Color:	Matt Black

Dimensions

Depth (mm):	30
Height (mm):	108
Width (mm):	30
Nett Weight (gram):	TBD
Gross Weight (gram):	TBD
Mounting Depth (mm):	10

2USB easyCharge DUO USB AC 18.0W/3.6A Matt Black

Technical Specifications

Rated Voltage:	220-250 V AC
Rated Frequency:	50.0 Hz
Rated Current:	16A
Rated Load:	3680W
Input Current:	Max. 500 mA
Input terminals	Screw terminals
Input wiring:	1,5mm ² - 2*2,5mm ² rigid, rigid-stranded or flexible
Stripping Length (mm):	11
Overvoltage Category (OVC)	III
Output Voltage:	220-250 V AC
Socket Type IEC:	Type F
Output Ports:	USB-A, USB-C
USB Protocollen:	Smart IC to enable efficient charging
Output Current:	
USB-A	2.4 A/5.0 V DC
USB-C	3.8 A/5.0 V DC
Output power:	18.0W (Total output power is shared between the USB ports)
Energy Efficiency (%)	>=80%
Stand-by Power (mW)	<= 50
Expected lifetime at Full Load (h)	20000
Operating Temperature	0 - +40°C
Storage Temperature	-20°C - +80°C

2USB easyCharge DUO USB AC 18.0W/3.6A Matt Black

Standards

Directives	Reference standards	National Norm
EMC	2014/30/EU	
LVD	2014/35/EU	
LVD	IEC 60884-1:2002 +A1:2006+A2:2013	
LVD	EN 62368-1:2014	
LVD	IEC 60884-1:2002 +A1:2006+A2:2013	NEN 1020:2019
LVD	IEC 60884-1:2002 +A1:2006+A2:2013	NEK IEC 60884-1:2002+A1:2006+A2:2013
LVD	IEC 60884-1:2002 +A1:2006+A2:2013	SS-IEC 60884-1:2013, SS 4280834:2013+T1
LVD	IEC 60884-1:2002 +A1:2006+A2:2013	SFS 5610:2015, SFS 5610:2015+A11:2016
REACH	Regulation (EC) No 1907/2006 & Regulation (EC) No 1272/2008	
RoHS	Directive 2011/65/EU & Directive 2015/863	
VDE 0620	DIN VDE 0620-1:2016+A1:2017	

Certifications

- CB report
- KEMA-KEUR