



Power Bank - XT-20000QC3

- Reliable energy for your application
- High quality cells
- Customized settings possible (Voltage)
- Long-life series
- DC output up to 24V



RoHS compliant



Pb free



REACH compliant



Conflict mineral free

TECHNICAL DATA

Part number	249851
Battery type	Lithium Ion
Capacity	20400mAh (3.7V) / 75.5Wh
Connections	1x USB Standard Output 1x USB Q3 Output 1x DC Socket (OUTPUT/INPUT) 1x Micro-USB socket (INPUT)
Input	1 x Micro USB 5V 2.1A 1 x DC Socket 13V-20V 3A max.30W
Output	1 x USB 5V 2.1A 1 x USB QC3 3.8V-12V/max.18W DC Socket 5/6/9/12/15/16.5/19/20/24V 50 Watt continuous / max.65W
Dimensions	174 x 78 x 21.5 mm
Weigth	450g

DELIVERY CONTENT

- Powerbank XTPower XT-20000QC3
- USB cable
- DC cable 2m
- Car charging adapter for DC socket
- 8 Notebook and Netbook Adapter
 - A = Sony, Fujitsu, Panasonic - 6.0x4.25mm
 - C = IBM, Acer, Toshiba, Dell, Asus - 5.5x2.5mm
 - D = Asus, HP, NEC, Toshiba, BenQ - 5.5x2.1mm
 - E = Acer, Toshiba, Sony - 5.5x1.7mm
 - F = Samsung - 4.8x1.7mm
 - H = Asus, HP, NEC, Delta, Compaq - 5.0x1.0mm
 - I = Dell, HP - 7.4x5.0x0.6mm
 - K = IBM, Lenovo, Sony - 7.9x5.4x0.9mm

OUTSTANDING FEATURES

- Simultaneously charging and discharging
- Power bank for industrial and professional applications
- Automatic switch off at DC port below 4W
- Also available without automatic switch off at DC output
- Also available with power supply
- Boarding with all airlines (<100Wh)

ADDITIONAL DATA

Life expectancy	approx. 500 charging cycles
Dimensions DC round socket	5.5mm x 2.1mm
Charging time	approx. 3 hours from 0% to 100%
Charging temperature	0 °C - 45 °C
Operating temperature	-20 °C - +60 °C
Safety	Overcharge protection Discharge protection Short circuit protection
EAN/GTIN	4250637212888



SCOPE OF DELIVERY

