


For help & information
email: sales@scanstrut.com
tel: +44 (0) 1392 531280



	A	B	C	D	E
	mm / inches	mm / inches	mm / inches	mm / inches	mm / inches
DS6	30/1.18	6/0.24	27.0/1.06	17/0.67	2-6/0.08-0.24
DS16	39/1.53	16/0.63	36.5/1.44	19/0.75	2-8/0.08-0.31
DS21A	49/1.93	21/0.83	45.7/1.8	20.5/0.81	4-9/0.17-0.31
DS21B	49/1.93	21/0.83	45.7/1.8	20.5/0.81	9-14/0.35-0.55
DS30	59/2.32	30/1.18	56/2.2	20.5/0.81	9-14/0.35-0.55
DS40	69/2.72	40/1.57	66/2.6	21.7/0.85	12-15/0.4-0.59

Please note: When ordering your Deck Seal please specify -S for Stainless steel and -P for Plastic.
e.g. DS16-P

Bung dimensions for different models (included in the package)

	2/0.08 mm / inches	3/0.12 mm / inches	4/0.16 mm / inches	5/0.20 mm / inches	6/0.24 mm / inches	7/0.28 mm / inches	8/0.31 mm / inches	9/0.35 mm / inches	10/0.39 mm / inches	11/0.43 mm / inches	12/0.46 mm / inches	13/0.51 mm / inches	NO HOLE
DS6	✓	✓	✓	✓	✓								✓
DS16		✓	✓			✓							✓
DS21A			✓	✓		✓							✓
DS21B								✓		✓		✓	✓
DS30								✓		✓		✓	✓
DS40											✓		✓

Please note: ✓ = one bung

SCANSTRUT®