

Item no.: 2898736

Data Sheet

Cable specification			
STYLE		H07RN-F 4G1.5	
Standard		EN50525	
Applications		Heavy outdoor wire	
Construction Details:			
Test Item		Unit	4G1.5
Conductor	Material		Copper
	Construction		30/0.237±0.005
	Conductor DC resistance at 20°C ≤		20°C ≤ 13.3Ω/km
Core Insulation	Material		EPDM
	Avg. thickness	mm	0.8
	Min. thickness	mm	0.62
	Over Diameter	mm	3.15±0.10
	Surface		Smooth
	Colors		Yellow/green、brown、black、grey
lay	filler		Cotton yarn
Jacket	Material		CPE
	Avg. thickness	mm	1.7
	Min. thickness	mm	1.35
	Over Diameter	mm	11.0±0.40
	Surface		Smooth
	Colors		BLACK
Marking	◁VDE ▷ 40015999 H07RN-F 450/750V 4G1.5mm ² RIFENG		

