

Item no.: 2898740

Data Sheet

SPECIFICATION			
STYLE		H07RN-F	
Standard		EN50525-2-21	
Applications		Heavy duty rubber cable	
Construction Details:			
Test Item		Unit	5G6
Conductor	Material	mm	Bare Copper
	Construction	mm	84/0.284±0.01
	Conductor DC resistance at 20°C ≤	Ω/km	3.3
Core Insulation	Material		EPDM
	Avg. thickness	mm	1
	Min. thickness	mm	0.8
	Colors		Green/yellow,blue,brown,black,gray
Jacket	Material	CPE	
	Avg. thickness	mm	2.5
	Min. thickness	mm	2.03
	Over Diameter	mm	18.9±1
	Surface		Smooth
	Colors		Black
marking	<VDE> 40015999 H07RN-F 450/750V 5G6mm² RIFENG		

