



WS 9456

Thermo-Hygrometer

- Quartz clock
- Indoor temperature display
- Indoor humidity display
- Trend display for temperature and humidity
- MIN/MAX memory
- Colored indoor comfort indicator
- Backlighting
- Wall mounting or table standing

Specifications

Thermo-Hygrometer

Dimensions (WxHxD): 81 x 98 x 15 mm

Power: 2 x CR2032 (included)

Temperature measuring range:

-9,9°C to 49,9°C

Humidity measuring range: 20% to 95%



EAN: 4029665094564