



U4X

**DAB+ / FM-RDS / Bluetooth / AUX / TWS / USB Playback
Ultra Rugged Dustproof / Waterproof Digital Radio**



Color

Black

dab+ NFC Bluetooth® IP65 Dustproof Waterproof

Main Features

- 50 Station Presets (25 DAB+/25 FM)
- Bluetooth 5.0 with NFC for Easy Pairing (A2DP/AVRCP)
- Supports TWS Multi-Speaker Pairing for Stereo Sound
- USB Playback to Play Your Own Favorite List
- 165mm Premium Dual Coil Speaker
- Station Auto Scanning
- Premium Easy to Read TFT Display with Backlight
- 2 Alarm Timers by Radio or Buzzer
- Adjustable Alarm Volume
- HWS (Humane Wake System) Buzzer and Radio
- Adjustable Sleep Timer
- Adjustable Tuning Step
- Rotary Bass / Treble / Mid Control
- Loudness On/Off
- Easy Cable Storage
- Roll-Cage Design for Shock Resistant
- IP65 Certified for Dustproof and Waterproof
- AUX-In for Additional Audio Sources
- Operates on Rechargeable Lithium Batteries
- DC-Out (5V/1A) USB Type-A Socket for Charging Mobile Devices
- I/O Ports: DC-In / AUX-In / USB Type-A

• EAN-code: 47.11317.997562.9 (BLACK)

Dimensions:

Dim. Unit : 298 x 268 x 342 mm (WxDxH)

Net / Gross weight of single device : 4.93 / 5.5 (kg)

Net / Gross weight of packaging : 11 / 11.9 (kg)

Container quantity :

20' ft : 800 (pcs)

40' ft : 1600 (pcs)

