



## WATERPROOF V 1500

26/45W 830/840 IP66

Discover our new technical product range: SLVtec. With state-of-the-art LED technology, we offer energy-efficient and functional lighting solutions for indoor and outdoor use. From wet room lights to high-bay spotlights – our high-quality products impress with functionality and a fair price-performance ratio. These include the WATERPROOF V light, which is protected against strong jets of water thanks to protection code IP66 and is also available as a DALI version. The light colour (3000K/4000K) and light intensity (3860lm/4130lm) can be easily changed via dip switches. The pre-installed through-wiring kit allows two lights to be connected quickly and easily. Installation is also extremely easy thanks to the removable equipment rack. Decide in favour of SLVtec today.

## TECHNICAL DATA

Item no.	1007491
IP Code	IP 66
Impact resistance class	IK 08
Assembly	Surface
Assembly details	Ceiling, Wall
Number of through-wires	30
Primary nominal voltage	220-240V ~50/60Hz
Secondary power / voltage	350/300/250 mA
Safety class	I
Wattage	45 W
Minimum ambient temperature	-20 °C
Maximum ambient temperature	40 °C
Number of luminaires at LS B16A	36
Number of luminaires at LS C16A	57
Level of inrush current	25 A
Duration of inrush current	135 µs
Stroboscopic effect (SVM)	0.04
Lumen	5670/5970 lm
Colour temperature	3000/4000 Kelvin
Color	grey
CRI	80
LXXBXX data	L80B10

## Light Source



<b>Service life</b>	50000 h
<b>Risk Group</b>	0
<b>Length</b>	153.6 cm
<b>Width</b>	8 cm
<b>Height</b>	7.6 cm
<b>Net weight</b>	1.9 kg
<b>Gross weight</b>	2.033 kg