



## DOWNLIGHT V 150

9/15W 830/840 IP54

Discover our new technical product range: SLVtec. With state-of-the-art LED technology, we offer energy-efficient and functional lighting solutions for indoor and outdoor use. From wet room lights to high-bay spotlights – our high-quality products impress with functionality and a fair price-performance ratio. These include the DOWNLIGHT V 150 recessed light, available in white or black with a flat or slightly recessed cover. With a power consumption of 9W or 15W, the light colour (3000K/4000K) and light intensity (1750lm/1900lm) are adjustable via dip switch. For this purpose, the DOWNLIGHT V 150 is quickly and easily installed thanks to the integrated connection box of the LED driver. Decide in favour of SLVtec today.

## TECHNICAL DATA

Item no.	1007509
IP Code	IP20/54
Impact resistance class	IK 02
Assembly	Recessed
Assembly details	Ceiling with Acc.
Number of through-wires	15
Primary nominal voltage	220-240V ~50/60Hz
Secondary power / voltage	250/400 mA
Safety class	II
Wattage	15 W
Minimum ambient temperature	-20 °C
Maximum ambient temperature	40 °C
Number of luminaires at LS B16A	39
Number of luminaires at LS C16A	66
Level of inrush current	7.6 A
Duration of inrush current	420 µs
Stroboscopic effect (SVM)	0.1
Lumen	1750/1900 lm
Colour temperature	3000/4000 Kelvin
Beam angle	105 °
Color	black
CRI	80

## Light Source

	
--	---

## Accessories

1007482	DOWNLIGHT V 150 , slightly recessed cover white
1007481	DOWNLIGHT V 150 , flat cover black
1007480	DOWNLIGHT V 150 , flat cover white
1007483	DOWNLIGHT V 150 , slightly recessed cover black

LXXBXX data	L70B50
Service life	50000 h
Risk Group	0
Height	3.9 cm
Diameter	12.3 cm
Net weight	0.221 kg
Gross weight	0.236 kg
Shape of cut-out	round
Installation depth	5.5 cm
Installation diameter	15 cm