




Modell/ <i>model</i>	L	l	B	b	H
EG 1230 F(L)	125	113.2 ^{+0.4} _{-0.2}	67	55.2 ^{+0.3} _{-0.2}	31
EG 1240 F(L)	125	113.2 ^{+0.4} _{-0.2}	67	55.2 ^{+0.3} _{-0.2}	41
EG 1250 F(L)	125	113.2 ^{+0.4} _{-0.2}	67	55.2 ^{+0.3} _{-0.2}	51
EG 1530 F(L)	150	138.2 ^{+0.5} _{-0.3}	82	70.2 ^{+0.3} _{-0.2}	31
EG 1545 F(L)	150	138.2 ^{+0.5} _{-0.3}	82	70.2 ^{+0.3} _{-0.2}	46
EG 1560 F(L)	150	138.2 ^{+0.5} _{-0.3}	82	70.2 ^{+0.3} _{-0.2}	61
EG 2030 F(L)	200	188.2 ^{+0.6} _{-0.3}	112	100.2 ^{+0.4} _{-0.2}	31
EG 2050 F(L)	200	188.2 ^{+0.6} _{-0.3}	112	100.2 ^{+0.4} _{-0.2}	51
EG 2070 F(L)	200	188.2 ^{+0.6} _{-0.3}	112	100.2 ^{+0.4} _{-0.2}	71

Weitere Maße siehe Standard-Gehäuse ohne Folientastaturfläche!/
Other dimensions on standard enclosure without membrane keypad surface!

Zeichnungs-Nr. / *Drawing-No.:*
3K 5010.353.02

Artikel / *Article*:

EG F(L)

OT ohne GWDBU/top part without GWDBU

Katalogzeichnung/ *Catalogue drawing*[illegible]

Ä.Nr/ Alt-No.:	Datum/ Date:
-------------------	-----------------

DISK:	2 801 147
Datum/Date:	10.01.94 OK



BOPLA

A Phoenix Mecano Company