



CU34P3CV

34 inch (86.36 cm) LCD MONITOR

34" WQHD curved IPS display for immersive viewing and enhanced productivity

General

Model name	CU34P3CV
EAN	4038986110730
Product Line	Pro-line
Series	P3
Channel	B2B
Classification	Mainstream
Section	Business
Launch date	2023-02-21T11:20:59+00:00
Continent	Europe
Product status (EU)	Launch

Screen

Resolution	3440x1440
Refresh rate	100Hz
Screen size (inch)	34 inch
Screen size (cm)	86.36 cm
Flat / Curved	Curved
Curvature Radius	1500R mm
Backlight	WLED
Panel Type	VA
Aspect ratio	21:9
Display Colours	16.7 Million
Panel Colour in Bits	8
Pixel Pitch	0.23175
Pixels per Inch	110
Response time (GtG)	4 ms
Contrast (static)	3000:1
Contrast (dynamic)	20M:1
Brightness (typical)	300 cd/m ²
Viewing angle (CR10)	178/178 °
Hard Glass	Antiglare + 3H
OSD languages	EN, FR , ES, PT, DE, IT, NL, SE, FI, PL ,CZ, RU, KR, CN (T), CN (S), JP

Exterior

Monitor colour	Black
Bezel Type	3-sided frameless
Removable Stand	✓
Cable Management System	✓

Ergonomics

Vesa Wallmount	100x100
Tilt	-5/23 ° °
Swivel	-175/175 ° °
Height Adjust Amount	150mm

Connectivity and Multimedia

Signal Input	HDMI 2.0 x 1, USB-C (DP Alt Mode), DisplayPort 1.4x1
USB-C Features	DP alt mode, Data Transfer (USB upstream), Power Delivery 65W
USB input	USB 3.2 (Gen1) x4 & USB-B 3.2 x1
USB Hub	✓
USB fast charge	✓
RJ-45	✓
KVM	✓
HBR3	✓

Multimedia

Built-in Speakers	5 W x 2
Audio output	Headphone out (3,5mm)

Features

Flicker-free	✓
PxP (PIP, PBP)	✓
Kensington Lock	✓

Sustainability

HF	✓
----	---

Power / Environmental

Powersupply	Internal
Powersource	100 - 240V 50/60Hz

Warranty

Warranty Period	3 Years
-----------------	---------

What's in the Box?

HDMI cable	1,8 m
Displayport Cable	1,8 m
USB cable	USB Type-C to C/A m
Power Cable C13	1,8 m