

Baton 4

DESIGNED TO STAND OUT

MAX OUTPUT	MAX RUNTIME	MAX THROW
1,300 lumens	30 days	170 meters

*This information is for market reference only. Please do not make it public.



Regal Blue



Black



Candy Cane



OD Green

MARKET APPLICATIONS

Camping & Hiking & Mountaineering & Household

UPC :

6975498002918 (Black)
6975498006404 (OD Green)
6975498006428 (Regal Blue)
6975498006374 (Candy Cane)

DESCRIPTION

The Baton 4 is the upgraded version of Olight's popular Baton 3. Equipped with a high-performance LED and TIR lens for a soft and balanced beam, this extremely compact light delivers an incredible maximum beam of 1,300 lumens, reaching up to 170 meters. The flashlight features a laser micro-perforated indicator that intuitively shows the remaining brightness and battery life. It is powered by a customized rechargeable 650mAh lithium-ion battery and can last up to 30 days in Moonlight mode. The upgraded anti-slip texture looks exquisite and enhances grip. The Baton 4 is the ultimate pocket light in terms of performance and convenience.



FEATURES

- **Small yet powerful:** The Baton 4 flashlight delivers 1,300 lumens and has a 170-meter beam distance. It's compact and high-performing, perfect for everyday carry.
- **Upgraded indicator:** The flashlight features a laser micro-perforated indicator that intuitively shows remaining brightness and battery life.
- **Durable metal switch:** The upgraded metal switch adds durability to the flashlight, making your every press more solid and enjoyable.
- **Extended battery life:** With an upgraded 650mAh lithium-ion battery, the Baton 4 lasts up to 30 days in moonlight mode.
- **Easy MCC charging:** Attach the light to metal surfaces for hands-free use or snap it to an MCC for convenient charging.

OUTPUT

SPECIFICATIONS	Turbo	High	Medium	Low	Moonlight	STROBE
	1,300±600±300 lumens	600±300±60 lumens	60 lumens	12 lumens	0.5 lumens	13Hz at 1,300 lumens
	1.5+2.5+73 minutes	7+72+16 minutes	8 hours	35 hours	30 days	
	170 meters	110 meters	38 meters	18 meters	N/A	
	7,225 cd	3,025 cd	361 cd	81 cd	21 cd	

* Note: All data above are test results according to ANSI/NEMA FL 1-2009 standards.

LIGHT SOURCE

High Performance CW LED

DIMENSIONS

Length: 2.48in/63mm
Head Diameter: 0.83in/21mm
Body Diameter: 0.83in/21mm

WEIGHT

1.85oz/52.5g (Including Battery)

BODY MATERIAL

Aluminum Alloy

POWERED BY

3.6V 650mAh 2.34Wh

WARRANTY

Lifetime Warranty in the USA, Australia, Germany, France and China.
5 Year Warranty in other countries and regions.

IN THE BOX

Flashlight (Battery and Pocket Clip Included) x1
MCC 1A Magnetic Charging Cable x 1
Pouch x1
User Manual x1

WATERPROOF IPX8



DROP TEST



COMPLIANCE



olightworld.com © Olight 10/24/23 V1

Made in China

Note: There are slight differences between the picture and the real item caused by light color temperature. All the pictures are for reference only.