

CRYSTAL


WARRANTY YEARS


Compact multi flashlights with additional type of light


















CTCLING



Compact, lightweight and stylish Crystal series multi flashlights are a multifunctional alternative to the usual keychain models. Design, body material and special arrangement of LEDs provide wide beam angle of 140°, optimal for use at a close distance. The flood beam makes Crystal flashlights an excellent main or additional light source for jogging, cycling or day-to-day tasks.

The series includes Crystal and Crystal WRB models. Additional red light of the Crystal model is suitable for performing work in the dark and for maintaining night vision when turning the flashlight on and off: in a camping tent, when observing the stars, for fishing or cycling. Besides the white light LED, Crystal WRB is equipped with the LED for use as a red-blue warning signal.

Capacious for the models of the given size battery eliminates the need to charge the flashlight for 50 days of continuous use in the minimum brightness mode. The flashlight does not take up much space in the bag, it easily fits in a pocket and is securely attached to a belt, or a backpack strap. The headband in the set allows for hands-free operation.







1 HEADLAMP

Soft elastic headband. Specially designed body with thought-out optical elements provides comfortable beam angle with minimum loss of light for use at a close distance.

2 EVERY DAY CARRY LIGHT

Lightweight and compact body made from durable plastics. Possibility to attach to bag, pocket, strap or cap using a clip.



3 KEYCHAIN LIGHT

Ring for keys made from durable materials.



4 BICYCLE LIGHT

Secure rubber rings for installation on a bicycle. Constant white light and white Beacon to use as headlight or running light. Constant red light and red Beacon for rear light (Crystal).



5 LAMP MODE

Works directly from a Powerbank or any USB adapter.



6 WARNING LIGHT (CRYSTAL WRB)

Red-blue beacon, fully luminous body, steel clip to attach to clothes or belt.



5 SHELL COLORS TO CHOOSE FROM:

Red Ruby Yellow Amber Green Jade Blue Sapphire Grey Onyx

- Convenient operation with one button, double click to change the light color
- Unique fully luminous body and several shell color options to choose from
- Built-in Li-Pol 600 mAh battery charges with any Micro USB cable
- · Color indication of charging process
- IP67 standard: reliable protection from dust and submersion at 1 meter for 30 minutes.
 Withstands fallings from up to 10 meters
- Red light of the Crystal model is almost invisible for animals, fish and insects, comfortable for night vision



CRYSTAL





MAX LUMENS

50/30
DAYS RUNTIME





WHITE, RED



RECHARGEABLE

Built-in battery charges with any Micro USB cable

DIMENSIONS

63х43х15 мм Weight 34 g



5 in 1 Headlamp, Every Day Carry, Keychain, Bicycle, Lamp


Multifunctional flashlight with white and red LEDs, additional mounts for use as headlamp, every day carry or bicycle light.

SET DESCRIPTION

- **1** flashlight with built-in battery,
- 2 headband, 3 installation rings for bicycle,
- **4** clip pad for bicycle, **5** user manual in eight languages











CRYSTAL WRB





MAX LUMENS

(3)

50

DAYS RUNTIME



 \bigcirc \bigcirc

WHITE LIGHT,

RED-BLUE BEACON



RECHARGEABLE

Built-in battery charges with any Micro USB cable

DIMENSIONS

63х43х15 мм Weight 34 g






6 in 1 Headlamp, Every Day Carry, Keychain, Bicycle, Lamp, Warning

Version of Crystal with red-blue beacon, designed for use by law enforcement officers as a warning signal.

2

SET DESCRIPTION

- 1 flashlight with built-in battery,
- 2 headband, 3 installation rings for bicycle,
- 4 clip pad for bicycle, 5 user manual in eight languages





SPECIFICATION

| | | Crystal | | Crystal WRB |
|--|---|---|---|--|
| | | White light | Red light | |
| Light output | | 150 lm | 30 lm | 150 lm |
| Beam distance | | 12 m | 5 m | 12 m |
| Hotspot: Spill | | 70° : 140° | | 70° : 140° |
| Brightness stabilization type | | Digital | | Digital |
| Number of modes | | 5 | 5 | 6 |
| Modes / Runtimes | Main3 Main2 Main1 Firefly Beacon Red-blue Beacon | 150 lm / 2 h 15 min 36 lm / 8 h 10 min 5 lm / 54 h 0.1 lm / 50 d 150 lm / 1 Hz / 9 h 50 min | 30 lm / 3 h 12 lm / 9 h 15 min 2 lm / 54 h 0.1 lm / 30 d 30 lm / 1 Hz / 13 h 30 min | 150 lm / 2 h 15 min 36 lm / 8 h 10 min 5 lm / 54 h 0.1 lm / 50 d 150 lm / 1 Hz / 9 h 50 min •30 lm •17 lm / 1.5 Hz / 3 h 25 min |
| Power source (built-in) | | Li-Pol 600 mAh | | Li-Pol 600 mAh |
| Length / width / height (without clip) | | 63 mm / 43 mm / 15 mm | | 63 mm / 43 mm / 15 mm |
| Weight | | 34 g | | 34 g |
| Submersion and Impact resistance | | Depth up to 1 meter for 30 minutes (IP67 standard). Height up to 10 meters | | Depth up to 1 meter for 30 minutes (IP67 standard). Height up to 10 meters |

All the above specifications are test results based on ANSI/NEMA FL1-2009 Standard. The tests are performed using the battery included in the set. The data may vary due to environment, heat dissipation and other factors.

| CRYSTAL |
|---------|
| |

Grey Blue 6957713003139 F07001G 6957713003146 F07001B Green 6957713003153 F07001GR Yellow 6957713003160 F07001Y Red 6957713003559 F07001R

CRYSTAL WRB

6957713003733 F07201B Blue Grey 6957713003726 F07201G

BENEFITS OF WORKING WITH ARMYTEK

Armytek is a world famous manufacturer of high-tech flashlights, chargers and accessories. All Armytek products perfectly meet the buyer's requirements. We focus on quality and reliability: smart lineup allows us to thoroughly think through every detail before launching mass production.



HIGH PROFIT

Favorable conditions and flexible prices for bulk orders are ensured by own factories in China.



★ FAST SHIPPING

Warehouses around the world: the goods are always in stock and ready for shipment. Reduced costs and time of delivery, no additional custom fees required. Lower costs on shippings directly from the factories.



EXCEPTIONAL RELIABILITY

Minimum returns rate — less than 1% (competitors' rate is 5-7%). All products go through quality checking on test stands.



* LEGENDARY SERVICE

Full support and cooperation: from placing an order to warranty service. Professional issue management, fast repairs and exchange.



NO HASSLE WARRANTY

Up to 10 years unprecedented warranty.



OWN FACTORIES

Every step of the process is controlled by our European specialists at the factories.



Head office in Europe. Team of highly qualified specialists from defence, aviation, space and other specialized industries.



EXPERIENCE

Expert in the fields of mechanics, optics and electronics. We specialize in development and manufacturing of flashlights and battery chargers since 2009.



COMPONENTS

Powerful Cree, Nichia and Samsung LEDs, electronics by the USA and Japan, aircraft-grade aluminium, tempered glass, etc.



SMART LINEUP

Simple process of choosing a product, no bulky catalogs with a lot of similar variants. Only best models for client's needs.



MEW PRODUCTS

Armytek produces innovative and the most technically advanced products in the world.



PRIVATE LABEL, OEM/ODM

Creating new products, modifying our production models and personalizing them according to your needs.

MARKETING SUPPORT

We provide all the necessary promotional materials: leaflets, booklets, catalogs, etc.



CLIENTS' NEEDS RESEARCH

We systematically gather feedback to make sure that our products completely fit clients' needs and requirements.

