

Dual terminal stud M8 (5/16")

www.victronenergy.com



Dual terminal stud M8 (5/16")	
Max. current	150 A
Max. Voltage	70 VDC
Terminal diameter	M8 (5/16 inch)
Terminal height	17 mm / 0.67 inch
Terminal material	Stainless steel
Hex nut material	Stainless steel
Recommended torque	10 N·m / 90 lbf·inch
Busbar strip material	Tin-plated copper (1.0 x 13 mm)
Base material	Glass fiber reinforced nylon
Weight	70 g
Dimensions (hwxwd)	45 x 43 x 32 mm 1.8 x 1.7 x 1.3 inch

