
















Abox 160 Pro SL-10²




1:2



Abox 160 Pro-16²



Innenansicht/interior view



Kondenswasserl cher
bei Bedarf  ffnen
open condensate water
holes as required

Fehlende Ma e k nnen dem DXF
entnommen werden
missing dimensions are
provided in the DXF

Varianten/ variants
Abox 160 Pro L
Abox 160 Pro-16 ²
Abox 160 Pro SL-10 ²

Schutzvermerk ISO 16016 beachten. Refer to protection notice ISO 16016.



Massblatt/ dimension sheet
Abox 160 Standard/Pro
M-Abox 160

Ma stab
Scale

1:2

1 Freigeige

05.08.22

05.08.22

05.08.22