




# Javelot

BEAM BEYOND BOUNDS

MAX OUTPUT	MAX RUNTIME	MAX THROW	PEAK BEAM INTENSITY
			
<b>1,350</b> lumens	<b>72</b> days	<b>730</b> meters	<b>134,000</b> candela

\*This information is for market reference only. Please DO NOT make it public.



▲ MATTE BLACK



▲ OD GREEN

## MARKET APPLICATIONS

Everyday Carry  
Outdoors  
Law Enforcement

UPC: 6975498003687 (Matte Black)  
6975498005605 (OD Green)

## DESCRIPTION

The Javelot is a powerful, portable, long-range EDC flashlight. With 134,000 candela, it casts a focused beam up to 730m (798 yards) — the farthest in its size, allowing you to identify targets from a distance. The light features a handle of perfect length with pronounced knurling to ensure a comfortable and secure grip. Its dual switches allow for convenient operation. The metal side switch offers access to 5 output levels for everyday use, and the programmable tactical tail switch allows for quick deployment in tactical scenarios. It includes a holster and a pocket clip for convenient carry. Using a 5,000mAh 21700 battery, the Javelot provides up to 72 days of continuous Moonlight Mode illumination. Compatible with Olight remote switches and magnetic mounts (both optional), it can also serve as a rail-mounted light. The powerful Javelot is made to exceed your lighting needs in a wide range of scenarios, including search and rescue or hunting.



## FEATURES

- **Made to Throw:** With 134,000 candela, the Javelot casts its focused beam up to 730m (798 yards) — the farthest in its size, allowing you to identify targets from a distance.
- **Modest in Size:** The light features a handle of perfect length with pronounced knurling to ensure a comfortable and secure grip.
- **Dual Switches for Easy Operation:** It features a metal side switch for everyday use and a programmable tail switch for quick deployment in tactical scenarios.
- **Convenient Carry Options:** The light comes with a nylon-reinforced holster and a reversible two-way clip for versatile carry.
- **High-Capacity Battery:** With the 5000mAh 21700 battery, it provides 72 days of non-stop brilliance in Moonlight Mode. Then you can recharge it with a snap, even when it's docked in the holster.
- **Doubles As a Rail-Mounted Light:** Mount it on your set-up together with a remote switch (optional) for greater control in night hunting or tracking.

## OUTPUT

SPECIFICATIONS	Turbo	High	Medium	Low	Moonlight
	1,350~600 lumens	650~250 lumens	150 lumens	15 lumens	0.5 lumen
	2+155 minutes	170+120 minutes	30 hours	7.5 days	72 days
	730 meters	500 meters	200 meters	75 meters	15 meters
	134,000 cd	63,000 cd	9,400 cd	1,360 cd	55 cd
	13Hz				

\* All data above are test results according to ANSI/NEMA FL 1-2019 standards.

## LIGHT SOURCE

High Performance Cool White LED (5700K~6700K)

## DIMENSIONS

Length: 5.43in/138mm  
Bezel Diameter: 1.57in/40mm

## WEIGHT

6.95oz/197g (Including Battery)

## BODY MATERIAL

Aluminum Alloy

## POWERED BY

3.6V 5000mAh 21700 Rechargeable Li-ion Battery

## WARRANTY

Lifetime Warranty in Australia, China, France, Germany and the USA.  
5-Year Warranty in other countries and regions.

## IN THE BOX

Javelot (Battery Included) x 1  
MCC3 Magnetic Charging Cable x 1  
Holster x 1  
Pocket Clip x 1  
User Manual x 1

## Optional Accessories

sROD-7 Magnetic Remote Switch  
sROD Magnetic Remote Switch With Long Coil Wire  
X-WM03/X-WM02 Magnetic Mount  
E-WM25/EX-WM25 Mount  
M-WM Mount

### WATERPROOF IPX8



### DROP TEST



olight.com © OLIGHT 01/16/24 V1

Made in China

Note: There are slight differences between the picture and the real item caused by light color temperature. All the pictures are for reference only.