

DJ STAND

PORTABLE DJ BOOTH SYSTEM

D

BEDIENUNGSANLEITUNG

Omnitronic liefert dir mit diesem ultrakompakten Pult einen professionellen Look für deine DJ-Gigs. Gefertigt aus einem leichten und faltbaren Alurahmen bietet dir der DJ Stand eine Arbeitsfläche von 105 x 52 cm. Die Arbeitshöhe beträgt 95 cm. Der Auf- und Abbau ist in wenigen Augenblicken erledigt und das ganz ohne Werkzeug. Die Lycra-Bespannung erfüllt B1 und kann von hinten beleuchtet werden, um die Performance durch verschiedene Lichteffekte zu unterstützen. Im Lieferumfang ist eine praktische Transporttasche enthalten. Wechselcover und Platten zur Erweiterung sind als Zubehör erhältlich.


BESONDERE MERKMALE

- Leichtes Alu-Rahmengestell
- Nur 10,5 kg Gesamtgewicht
- Klappbar und leicht zu transportieren
- Schneller, werkzeugloser Aufbau
- Perforierte Ablage für eine optimale Luftzirkulation
- Abnehmbare Stretch-Bespannung für bequeme Reinigung

SPEZIFIKATIONEN

Modell:	Compact Mobile DJ Stand
Bestellnummer:	32000025
Arbeitsfläche:	105 x 52 cm
Maximale Belastung:	75 kg
Arbeitshöhe:	95 cm
Material:	Aluminium/Stahl
Textilcover:	Handwäsche nur bei 30 Grad Nicht im Trockner trocknen Erfüllt B1, nach dem Waschen neu imprägnieren
Transportmaß:	115 x 56 x 14 cm
Gewicht:	10,5 kg
Lieferumfang:	4-teiliger Alurahmen Perforierte Ablage Weißes Stretch-Cover Transporttasche

SICHERHEITSHINWEISE

 Bitte lies vor der Verwendung des Produkts diese Anleitung. Sie enthält wichtige Hinweise für den korrekten Betrieb. Bewahre diese Anleitung für weiteren Gebrauch auf.

- Dieses Produkt dient als Arbeitspult für DJ-Auftritte. Die Ablagefläche kann mit maximal 75 kg zentrisch belastet werden.
- Von der Gewährleistung ausgeschlossen sind alle Mängel, die durch unsachgemäße Behandlung, Beschädigung oder Reparaturversuche entstehen. Dies gilt auch für den normalen Verschleiß.
- Das Pult auf eine ebene, stabile Fläche stellen und gemäß umseitigem Diagramm aufbauen. Dabei darauf achten, dass keine Finger oder andere Körperteile eingeklemmt werden.
- Das Produkt ausschließlich gemäß den hier gegebenen Vorgaben nutzen. Ein falscher Aufbau kann zu einer zusätzlichen Belastung des Rahmens und der Komponenten führen.
- Das Pult nicht überladen und nicht darauf stehen oder sitzen.
- Das Produkt ist kein Spielzeug. Halte es vor Kindern und Tieren fern. Verpackungsmaterial nicht achtlos liegen lassen.
- Das Produkt ist bis auf eine gelegentliche Reinigung wartungsfrei. Zur Reinigung eignet sich ein angefeuchtetes Tuch. Das Textilcover wie angegeben reinigen.



PRO GEAR

WWW.OMNITRONIC.DE

EN

USER MANUAL

This ultra-compact Omnitronic stand creates a professional look for your DJ gigs. Made of a lightweight and foldable aluminum frame, the DJ stand offers you a workspace of 105 x 52 cm. The working height is 95 cm. The setup is done in no time at all and without any tools. The lycra covering meets B1 and can be backlit with various lighting effects to further support the performance. A practical transport bag is included in the delivery. Interchangeable covers and add-on corner shelves are available as accessories.


SPECIAL FEATURES

- Lightweight aluminum frame
- Total weight just 10.5 kg
- Foldable and easy to carry
- Fast, tool-free setup
- Open design provides optimal air circulation
- Removable stretch fabric for convenient cleaning

SPECIFICATIONS

Model:	Compact Mobile DJ Stand
Order code:	32000025
Shelf dimensions:	105 x 52 cm
Maximum load:	75 kg
Shelf height:	95 cm
Material:	Aluminium/steel
Textile cover:	Hand wash only at 30 degrees Do not tumble dry Meets B1, impregnate after washing
Transport dim.:	115 x 56 x 14 cm
Total weight:	10.5 kg
Package contents:	4-piece aluminum frame Perforated shelf White stretch cover Transport bag

SAFETY INSTRUCTIONS

 Please read these operating instructions carefully before using the product. They contain important information for the correct use of your product. Please keep them for future reference.

- This product serves as a work desk for DJ performances. The shelf can be loaded with a maximum of 75 kg (evenly distributed).
- The warranty does not cover faults caused by incorrect handling, damage or attempted repairs. The same applies to normal wear and tear.
- Place the stand on a flat, stable surface and set it up according to the diagram overleaf. Make sure that no fingers or other body parts become trapped.
- The product should only be used in accordance with the instructions given here. Incorrect setup may lead to additional stress on the frame and components.
- Do not overload the stand and do not stand or sit on it.
- This product is not a toy. Keep it out of the reach of children and pets. Do not leave packaging material lying around carelessly.
- This product is maintenance-free, except for occasional cleaning. Please use a slightly dampened cloth for cleaning. Clean the textile cover as specified.

MOUNTING

INSTRUCTIONS



AUFBAU | Bitte befolge die hier gezeigten Schritte, um das Pult korrekt aufzustellen.
SETUP | Please follow the steps shown here to set up the stand correctly.

