

Green Cell

PowerPlay^{10s}

Product card



Specification:

Name:	PowerPlay10s
Model:	PBGC02S
Capacity:	10 000 mAh (3.85V 38.5 Wh)
Rated Output:	6 930 mAh (5 V) 34.65 Wh ($\eta = 90\%$)
Input:	
USB-C1 Ultra Charge	5 V=2 A / 9 V=2 A (Max 18 W)
USB-C2 Power Delivery	5 V=3 A / 9 V=2 A (Max 18 W)
Output:	
USB-C1 Power Delivery	5 V=3 A / 9 V=2 A / 12 V=1.5 A (Max 18 W)
USB-A1 Ultra Charge	5 V=3 A / 9 V=2 A / 12 V=1.5 A (Max 18 W)
USB-A2 Ultra Charge	5 V=3 A / 9 V=2 A / 12 V=1.5 A (Max 18 W)
Total Output Power	18 W (Max)
Dimensions	140 x 72 x 14 mm (5.5 x 2.8 x 0.6 in)
Weight	197 g

Overcharge protection
Deep discharge protection

Short-circuit protection
Overload protection