

PH1 PH2 PH2 PH3 PZ1 PZ2 PZ2 PZ3

T9 T10 T15 T20 T25 T27 T30 T40v

1,5 2 2,5 3 3,5 4 5 6

5,5mm 6,5mm 2,0 2,5 3,0 4,0 5,0 6,0

PH2 PZ2 8mm 10mm

60mm