
xiaomi Desk Lamp Lite User Manual · 01

Руководство пользователя настольной лампы Xiaomi Desk Lamp Lite · 06
Manuale utente Xiaomi Desk Lamp Lite · 12
Manuel d'utilisation du Xiaomi Desk Lamp Lite · 17
Xiaomi Schreibtischlampe Lite Bedienungsanleitung · 22
Manual de usuario de Xiaomi Desk Lamp Lite · 27
Instrukcja obsługi Lampka biurkowa Xiaomi Lite · 32
Manual do utilizador do Candeeiro de secretária Lite Xiaomi · 37
Xiaomi Bureaulamp Lite Gebruikershandleiding · 42
Xiaomi Masa Lambası Lite Kullanım Kılavuzu · 47
Посібник користувача настільної лампи Xiaomi Desk Lamp Lite · 52

Read this manual carefully before use, and retain it for future reference.

Product Overview

Package Contents: Xiaomi Desk Lamp Lite, user manual, warranty notice




On/Off Button Instructions:
Press: Turn on/off the lamp.
Press and hold: Cycle through the three levels of brightness and release to stop at the current brightness.

Note: If the lampshade or lamp pole cannot be held in that position when the angle is adjusted, remove the detachable decorative cover and gently tighten the screw with a screwdriver.

Note: Illustrations of product and accessories in the user manual are for reference purposes only. Actual product and functions may vary due to product enhancements.

Lamp Adjustment



Precautions:

- " ⌂ "This lamp is for indoor use only. Self-disassembly or repair is not permitted.
- Do not expose the lamp to water or heat sources when using it. Do not use it in humid conditions for long periods of time. Do not cover the lampshade during use to avoid damaging the lamp or creating potential safety hazards.
- The external flexible cable or cord of this luminaire cannot be replaced; if the cord is damaged, the luminaire shall be destroyed.
- The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
- Do not adjust the lamp pole or lampshade beyond the normal angle of use by brute force, to avoid damaging the lamp or creating potential safety hazards.
- If the lamp shell is cracked, stop using the lamp immediately to avoid potential safety hazards.
- The power cord of the lamp is 1.5 m long, so please ensure a proper distance between the outlet and the lamp when using the lamp.
- When using the lamp, please adjust the lamp pole to the maximum angle (approx. 85°) as shown in the figure.
- The lamp must not be placed on a flat surface with an angle of inclination greater than 6°, otherwise the stability cannot be guaranteed.
- Do not adjust the lamp pole to an angle less than 85° when using the lamp, as this may not keep the lamp stabilized.
- This product contains a light source of energy efficiency class D.

Regulatory Compliance Information

WEEE Disposal and Recycling Information

All products bearing this symbol are waste electrical and electronic equipment (WEEE as in directive2012/19/EU) which should not be mixed with unsorted household waste. Instead, you should protect human health and the environment by handing over your waste equipment to a designated collection point for the recycling of waste electrical and electronic equipment, appointed by the government or local authorities. Correct disposal and recycling will help prevent potential negative consequences to the environment and human health. Please contact the installer or local authorities for more information about the location aswell as terms and conditions of such collection points.

CE EU Declaration of Conformity

We, Xiaomi Communications Co., Ltd., hereby declare that this equipment is in compliance with the applicable Directives and European Norms, and amendments. The full text of the EU declaration of conformity is available at the following internet address:
http://www.mi.com/global/service/support/declaration.html

Specifications

Model: 9290041693
Scope of Application: Indoor
Operating Temperature: -10°C to 35°C
Lumen: 840 lm
Color Temperature: 3900 K
Rated Input: 220-240 V~, 50/60 Hz, 0.06 A
Rated Input Power: 7.5 W (70 × 0.1 W/LED module)
PF (Power Factor) : 0.5
Color Rendering Index: Ra90
Net Weight: Approx. 0.56 kg
Item Dimensions: 400 × 413 × 125 mm

Non-replaceable light source

Non-replaceable control gear

Manufacturer: Xiaomi Communications Co., Ltd.
Address: #019, 9th Floor, Building 6, 33 Xi'erqi Middle Road, Haidian District, Beijing, 100085, China
For further information, please go to www.mi.com

User Manual Version: V1.0