



PRIME PX-2200



SPECIAL FEATURES

- ❖ ATX 3.1 and PCIe 5.1 Compatible
- ❖ Ultra-high Efficiency, 80 PLUS® Platinum Certified
- ❖ Fully Modular
- ❖ Native 12V-2x6 Cables
- ❖ Top-Quality 135 mm Fluid Dynamic Bearing Fan
- ❖ Digital Hybrid Fan Control
- ❖ Micro Tolerance Load Regulation (MTLR) [0.5 %]
- ❖ Super Low Ripple Noise [under 20 mV] *
- ❖ Cable-free Connection Design
- ❖ Gold Plated High Current Terminal (MB, CPU and PCIe)
- ❖ Multi-GPU Technology Support
- ❖ AC Input Range: 200 - 240 Vac only




* under 25 mV for 1000 W

POWER DISTRIBUTION

Model	+3.3 V	+5 V	+12 V	-12 V	+5 Vsb	Total Power
PRIME PX-2200	25 A	25 A	183.33 A	0.5 A	3 A	2200 W
	125 W		2200 W	6.0 W	15 W	



CONNECTOR QUANTITY

Cable								
Model	Main Power (24P / 20P) 610 mm	EPS 12 V / ATX 12 V (8P / 4P) 700 mm	12V-2x6 (12+4P) 700 mm	12V-2x6 (2x 8-pins to 12V-2x6) 700 mm	PCI-E (8P / 6P) 750 mm	SATA 950 mm	SATA 3.3 550 mm	Peripheral (4P) 690 mm
PRIME PX-2200	1	3	2	2	4	16	2	3

Compliance:   CB   CE   EAC    

Protection Features: OPP / OVP / UVP / SCP / OCP / OTP

Dimensions: 210 mm (L) x 150 mm (W) x 86 mm (H)

12 YEARS
WARRANTY

Specifications may change without prior notice



Headquarters sales@seasonic.com
USA ssa.sales@seasonic.com
Europe sse.sales@seasonic.com

www.seasonic.com