



CERTIFICATION RECORD

The company named below has been authorized by CSA International to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

File No: 044087_S_000

Class No: 3211 05 INDUSTRIAL CONTROL EQUIPMENT Motor Controllers -
Manual

SUBMITTOR

4703490 Telemecanique/Schneider Electric
Industries SAS
BP 660
Zone Industrielle No. 3
L'Isle d'Espagnac, 16340
France

FACTORIES

4612945 Schneider Electric A.S.
Cizovska 447
Pisek,
Czech Republic

September 21, 2007 (Replaces: October 19, 1998)

- Cam-operated controllers, 3-phase ac, the switching sections being assembled in various combinations as required for reversing, speed control etc., (not as star-delta control) for flush mounting or back-of-panel mounting, with the following max ratings at 600V unless otherwise noted: Types K1, K11, 10A, 300V ac HD, A300, 1 hp, 240V ac 3-ph, 1/2 hp, 120V ac, 3-ph, 0.33 hp, 240V ac 1-ph 2-pole; 1/6 hp, 120V ac 1-ph, 2-pole; K2 and K112, 12A, 300V ac HD, A300, 3 hp, 240V ac 3-ph, 1 hp, 240V ac 1-ph, 2-pole; 1-1/2 hp, 120V ac, 3-ph; 1/2 hp, 120V ac, 1-ph, 2-pole; K12 and K12CU, 12A, 1.5 hp 110V, 0.5 hp 110V ac, 1-ph, 2-pole, 150V ac HD; K13, 16A, 5 hp, 600V ac HD, quick connectors max 300V ac; K13CU, 16A, 5 hp, 3 hp, 1-ph, 2-pole, 600V ac HD, K3 and K16, 20A, 2 hp,

110V, 0.75 hp 110V ac 1-ph 2-pole, 150V ac HD; K16.1, 20A, 10 hp, 600V ac HD; K4 and K20, 25A, 20 hp; K5 and K32, 32A, 25 hp; K6 and K40, 45A, 40 hp; K7 and K60, 63A, 50 hp; K8 and K100, 110A, 60 hp; K9 and K200, 195A, 75 hp.

Note: The type designation of the above controllers is completed with letters and numbers, indicating the contact arrangement, switching combinations, the type of mounting and operating means.

/pg