



Power Bank - XT-24000DC-AO-120

- With high DC discharge output of 120W
- Reliable energy for your application
- High quality cells
- Customized settings possible (Voltage)
- DC output 5 to 24V



RoHS compliant



Pb free



REACH
compliant



Conflict
mineral free

TECHNICAL DATA

Part number	252220
Battery type	Lithium Ion
Capacity	24000mAh (3.7V) / 87Wh
Connections	1x USB-C (OUTPUT/INPUT) 1x USB-A QC3 Output 1x DC Socket (OUTPUT/INPUT)
Input	1 x USB-C 5A 100W 1 x DC Socket 12V-24V max.60W
Output	1 x USB-C PD20 100W max 1 x USB 5V-12V/max.18W DC Socket 5-24V max.120W
Dimensions	168 x 88 x 28 mm
Weight	540g

DELIVERY CONTENT

- Powerbank XTPower XT-27000DC-AO
- USB-C cable
- DC cable 2m
- 8 Notebook and Netbook Adapter
C = IBM, Acer, Toshiba, Dell, Asus - 5.5x2.5mm
D = Asus, HP, NEC, Toshiba, Acer - 5.5x2.1mm
E = Acer, Lenovo, Sony - 5.5x1.7mm
G = HP, Acer, Asus, Sony, Samsung - 4.0x1.7mm
HP = HP - 4.5x3.0mm
Dell = Dell - 4.5x3.0mm
M = Lenovo - 7.9x5.4x0.9mm
I = Dell, HP, Compaq - 7.4x5.0mm
- Power supply unit

OUTSTANDING FEATURES

- High Performance DC output 120W
- Simultaneously charging and discharging
- Power bank for industrial and professional applications
- Boarding with all airlines (<100Wh)

ADDITIONAL DATA

Life expectancy	approx. 500 charging cycles
Dimensions DC round socket	5.5mm x 2.1mm
Charging time	approx. 2.5 hours from 0% to 100%
Charging temperature	20 °C - 45 °C
Operating temperature	-20 °C - +60 °C
Safety	Overcharge protection Discharge protection Short circuit protection
EAN/GTIN	4250637213458



SCOPE OF DELIVERY

