

Digital Microscope Pro TX-277

with display



4.3" 4.3 Inch Display **50x** 50x Magnification **LED** LED Spotlight **▶** Photo & Video **MicroSD** MicroSD slot **1800 mAh** Battery



- 50x magnification
- 4.3 Inch IPS Display
- Display angle adjustment
- Adjustable holder
- 8 Illumination LED (adjustable)
- Photo and video function
- MicroSD card support (up to 32GB)
- PC connection

Technical specifications:

- Screen resolution: 480 x 272 px
- CMOS-Sensor size: 1/4"
- Focus mode: Manual
- Focus range: 10mm – 40mm
- Aperture: F4.5
- Camera angle: 16°
- Photo resolution: 10M, 7M, 5M, 3M, 2M, 1M; format: JPG
- Video resolution: 720P; format: AVI
- PC resolution and transmission rate: 1280 x 720px / 25fps
- Power: 1.9 W
- Working current: 380 mA
- Battery: built-in 1800mAh / 3,7 V
- Charging time: approx. 3h
- Working time: approx. 5h
- PC operating systems: Windows 10 or higher; Mac OS x 12 or higher
- Charging and signal interface: USB-C
- Operating temperature: 10°C to 45°C
- Material: ABS plastic
- Weight / Dimensions: 405 g / 20 x 12 x 16 cm

Package Contents: Digital Microscope Pro TX-277, support pole, holder, base, charging cable, user manual

Article Number: 5140

