






NOTES:

1. METALHOOD + COVER: ABS UL 94 V-0; METALLIZED
2. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
3. PRESS INSERT: ABS UL 94 V-0; METALLIZED
4. SHORT SCREWS: BRASS; NICKEL PLATED
5. LENS HEAD SCREWS: STEEL; NICKEL PLATED

TECHNICAL DATA:

- TEMPERATURE RANGE: - 33°C to + 90°C



ROHS compliant, exemption 6c/
ROHS konform, Ausnahme 6c

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1				
							material: SEE NOTES				
								date	name	title: PLASTIC HOOD 9pos. with straight cable exit	
								drawn 03.09.2014	Unkrüer		
				appd. 04.09.2014	Lehmenkühler						
				norm		dwg no: Ⓟ 16K1A3513					
1 x c	Ä21-0233	06.06.2024	JLE	d-old	16K2A171A						
3 x b	Ä 5304	03.09.2014	Unkrüer			part no: 165X13469X					
a	Original										
rev.	description	date	name			DIN-A3 sh: 1					