

6

5

4


3

2





1

used for: D-SUB

9pos.



15-37pos.

CABLE CLAMP:
9-37pos.

(f)

POS.	A	B	C	D	E	F	G	H	K	L	M	Part NO.
9	34.0	25.0	25.0	27.75	14.5	8.5	17.6	12.0	4.8	0.8	2.6	165X10909X
15	42.3	33.3	37.0	39.75	14.5	10.0	17.6	12.0	4.8	0.8	2.6	165X10919X
25	56.0	47.0	37.0	39.75	14.5	10.5	26.4	20.0	4.8	0.8	4.4	165X10929X
37	72.5	63.5	37.0	39.75	14.5	10.5	26.4	20.0	4.8	0.8	4.4	165X10939X

NOTES:

1. HOOD MATERIAL: ABS UL94 V0, METALLIZED
2. SCREWS: BRASS, NICKEL-PLATING
3. CABLE CLAMPS: STEEL, NICKEL-PLATING
4. MAX. MOUNTING TORQUE 0,15 Nm
RECOMMENDED MOUNTING TORQUE 0,1 Nm

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
1 x f	Ä 6805	27.07.2017	Lehmen
1 x e	Ä 6403	09.11.2016	Lehmen
2 x d	Ä 3961	06.04.2011	K.H.
2 x c	Ä 3525	14.12.2009	Henne
3 x b	Ä 1898	08.12.2003	Lehmen
a	Original		

tolerance



scale:

2:1

material:

SEE SPECIFICATION

title:

PLASTIC HOOD
9-37pos.

dwg no:

16K1A972

part no:

SEE TABLE

DIN-A
3
sh: 1/1

CONEC®