

SORTIMENTSKÄSTEN

ASSORTMENT BOXES



Bild Picture	Artikelnummer Item number	Inhalt Content	ESKA Serie	Norm Standard
	120.900	100 Stk. 100 Stk. 100 Stk.	520.600	IEC 60127-2-2
	121.800		521.000	DIN 41571-2
	122.800		522.500	IEC 60127-2-3
	120.950		520.500	IEC 60127-2-1
	122.850		522.700	IEC 60127-2-5

Bild Picture	Artikelnummer Item number	Inhalt Content	ESKA Serie	Norm Standard
	632.800	120 Stk.	632.600	IEC 60127-2-4
	632.820		632.200	Factory Standard
	632.830		632.300	Factory Standard
	520.800	200 Stk.	520.600	IEC 60127-2-2
	521.800		521.000	DIN 41571-2
	522.800		522.500	IEC 60127-2-3

Bild Picture	Artikelnummer Item number	Inhalt Content	ESKA Serie	Norm Standard
	E3520.800	360 Stk.	520.600	IEC 60127-2-2
	E3521.800		521.000	DIN 41571-2
	E3522.800		522.500	IEC 60127-2-3

Bild Picture	Artikelnummer Item number	Inhalt Content	Charakterik Characteristics		ESKA Produkt / Product
	522.805	200 Stk.	Träge/ time-lag	20 x 500 mA 20 x 1 A 20 x 1,6 A 20 x 2 A 20 x 2 A 20 x 3,15 A 20 x 3,15 A 20 x 4 A 20 x 4 A 20 x 6,3 A	522.514 522.517 522.519 522.520 522.720 522.522 522.722 522.523 522.723 522.525
	520.805	200 Stk.	Flink / fast acting	20 x 100 mA 20 x 250 mA 20 x 500 mA 20 x 2 A 20 x 2 A 20 x 2,5 A 20 x 3,15 A 20 x 4 A 20 x 5 A 20 x 6,3 A	520.607 520.611 520.614 520.620 520.620 520.621 520.622 520.623 520.624 520.625
	521.805	200 Stk.	Mittelträge / medium time-lag	20 x 200 mA 20 x 500 mA 20 x 630 mA 20 x 1 A 20 x 2 A 20 x 2,5 A 20 x 3,15 A 20 x 4 A 20 x 6,3 A 20 x 10 A	521.010 521.014 521.015 521.017 521.020 521.021 521.022 521.023 521.025 521.027
	E3523.800	360 Stk.	Flink / fast acting	20 x 1 A 20 x 1,6 A 20 x 2 A 20 x 3,15 A 20 x 4 A 20 x 6,3 A	520.617 520.619 520.620 520.622 520.623 520.625
			Mittelträge / medium time-lag	20 x 1 A 20 x 1,6 A 20 x 2 A 20 x 3,15 A 20 x 4 A 20 x 6,3 A	521.017 521.019 521.020 521.022 521.023 521.025
			Träge/ time-lag	20 x 1 A 20 x 1,6 A 20 x 2 A 20 x 3,15 A 20 x 4 A 20 x 6,3 A	522.517 522.519 522.520 522.522 522.523 522.525

Bild Picture	Artikelnummer Item number	Inhalt Content	Charakterik Characteristics		ESKA Produkt / Product
	E3523.801	360 Stk.	Flink / fast acting	10 x 500 mA	520.614
				10 x 630 mA	520.615
				10 x 800 mA	520.616
				10 x 1 A	520.617
				10 x 1,25 A	520.618
				10 x 1,6 A	520.619
				10 x 2 A	520.620
				10 x 2,5 A	520.621
				10 x 3,15 A	520.622
				10 x 4 A	520.623
				10 x 5 A	520.624
				10 x 6,3 A	520.625
			Mittelträge / medium time- lag	10 x 500 mA	521.014
				10 x 630 mA	521.015
				10 x 800 mA	521.016
				10 x 1 A	521.017
				10 x 1,25 A	521.018
				10 x 1,6 A	521.019
				10 x 2 A	521.020
				10 x 2,5 A	521.021
				10 x 3,15 A	521.022
				10 x 4 A	521.023
				10 x 5 A	521.024
				10 x 6,3 A	521.025
			Träge/ time-lag	10 x 500 mA	522.514
				10 x 630 mA	522.515
				10 x 800 mA	522.516
				10 x 1 A	522.517
				10 x 1,25 A	522.518
				10 x 1,6 A	522.519
				10 x 2 A	522.520
				10 x 2,5 A	522.521
				10 x 3,15 A	522.522
				10 x 4 A	522.523
				10 x 5 A	522.524
				10 x 6,3 A	522.525