







POS.	A -0.76	B -0.25	C	D -0.3	Part-No. Bulk Package	Part-No. © Single Package
9	31,19	16.79	25,00 ^{+0,12} _{-0,13}	6,12	165X16719X	165X16719XE
15	39,52	25.12	33,30 ^{+0,15} _{-0,1}	6,12	165X16729X	165X16729XE
25	53,42	38.84	47,04 ± 0,13	5,99	165X16739X	165X16739XE
37	69,70	55.30	63,50 ± 0,13	5,99	165X16749X	165X16749XE

NOTES:

1. SCREEN CAP: STEEL; TIN PLATED

(f)(c)(b) 2. MALE SCREWS: BRASS; NICKEL PLATED


(c)(b) 3. RETAINING CLIPS: STAINLESS STEEL

(d) 4. CONNECTOR IS PART MARKED: [PART-NO. CONEC ABC]

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
					date	name
3 x f	Ä 3968	11.05.2011	Lehm.	drawn	26.04.01	Parei
1 x e	Ä 3626	22.04.2010	K.H.	appd.	26.04.01	Mickenbecker
3 x d	Ä 3463	20.10.2009	Petker	norm		
2 x c	Ä 2440	10.02.2006	Lehm.	d-old		
2 x b	Ä 1872	29.10.2003	Lehm.			
a	Original					
rev.	description	date	name			

CONEC®

scale:	2:1	
material:	SEE NOTES	
title:	COVERED SCREEN CAP 9-37pos. for socket connector	
dwg no:	16K1A184A	DIN-A4
part no:	SEE TABLE	
		sh: 1