



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	07OCT2017	GK	DB
	A1	UL TABLE UPDATED	06JUN2018	GK	DB

LABEL AND LINER DESIGN



PRESENTATION



OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 1250

All dimensions in mm [Inch]

TE PN: 2322818-1

UL-MARKING AND LABELLING SYSTEMS		
PGJ12 - Printing Materials - Component (UL 969)		
PGJ18 - Printing Materials Certified for Canada - Component (CSA C22.2 No. 0.15)		
File: MH17292	Product design: PL-9	Ribbon: TTB-XXXSC/YYYYAQ529

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.5 [.020]
VERTICAL REPEAT:	±0.5 [.020]*
HORIZONTAL REPEAT:	±0.5 [.020]*
LABEL POSITIONING:	±0.5 [.020]*
LEFT MARGIN:	±0.5 [.020]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL SEE TABLE	FINISH GLOSSY

MATERIAL		POLYESTER WHITE GLOSS	
ADHESIVE TYPE		ACRYLIC PE FOAM	
LINEAR		BROWN KRAFT	
DWN GOPALAKRISHNA HV	07OCT2017	TE Connectivity	
CHK D.BURGAT	07OCT2017		
APVD D.BURGAT	07OCT2017	NAME	
PRODUCT SPEC TTDS-245		PANEL LABEL-WHITE 35.0 x 18.0mm [1.378 x 0.709inch]	
APPLICATION SPEC		-	
WEIGHT 0.297 _g	SIZE A2	CAGE CODE FB1U7	DRAWING NO PL-035018-1.25-9
CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
		REV A1	