



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	21SEP2017	GK	DB
	A1	UL TABLE UPDATED	06JUN2018	GK	DB

LABEL AND LINER DESIGN

PRESENTATION



OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 1500

All dimensions in mm [Inch]

TE PN: 2322686-1

UL-MARKING AND LABELLING SYSTEMS		
PGJ12 - Printing Materials - Component (UL 969)		
PGJ18 - Printing Materials Certified for Canada - Component (CSA C22.2 No. 0.15)		
File: MH17292	Product design: PL-9	Ribbon: TTB-XXXSC/YYYYAQ529

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.5 [.020]
VERTICAL REPEAT:	±0.5 [.020]*
HORIZONTAL REPEAT:	±0.5 [.020]*
LABEL POSITIONING:	±0.5 [.020]*
LEFT MARGIN:	±0.5 [.020]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL SEE TABLE	FINISH GLOSSY

MATERIAL		POLYESTER WHITE GLOSS			
ADHESIVE TYPE		ACRYLIC PE FOAM			
LINEAR		BROWN KRAFT			
DWN GOPALAKRISHNA HV 21SEP2017	CHK D.BURGAT 21SEP2017	NAME D.BURGAT			
APVD D.BURGAT 21SEP2017	PRODUCT SPEC TTDS-245	PANEL LABEL-WHITE 27.0 x 13.0mm [1.063 x 0.512inch]			
APPLICATION SPEC —	WEIGHT 0.165 _g	SIZE A2	CAGE CODE FB1U7	DRAWING NO PL-027013-1.5-9	RESTRICTED TO —
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV A1