
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

PROJECT	PRJ–16–000909157
PART NO.	X–2308342–X
DESCRIPTION	FULL METAL HOODS SIZE 3
CUSTOMER	GENERAL MARKET


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR–16–013123	19SEP2016	KK	GG


1–2308342–3



1–2308342–7



Case



NOTES:

1. FINISH:
   1–2308342–1 TO 1–2308342–8 – CASE RAW
   1–2308342–9 TO 2–2308342–6 – CASE NICKEL–PLATED
2. LOCKING SCREWS: NICKEL–PLATED
   OTHER SCREWS: ZINC–PLATED
3. TEMPERATURE RANGE: –40°C TO +90°C
4. CABLE DIAMETER WITH EXTERNAL DIAMETER CABLE CLAMP: 4–14 mm.
5. STRAND DIAMETER OF CRIMP FLANGE: 2.7–8.7 mm.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 2768–m DIN 16901 130B

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL: –

FINISH: –

DWN	KIRAN K 02AUG2016
CHK	GUNASEKHAR G 02AUG2016
APVD	GUNASEKHAR G 02AUG2016
PRODUCT SPEC	–
APPLICATION SPEC	–
WEIGHT	

TE Connectivity

NAME: FULL METAL HOODS SIZE 3

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C–2308342	–

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 2 | REV A1

2308342

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1-2308342-8	FULL METAL HOODS SIZE3-8	1-2308334-6	1-2308334-4	LOCKING SCREW (M3 LONG KNURLED)	LOCKING SCREW (M3 SHORT KNURLED)	S OVER	M3	72
1-2308342-7	FULL METAL HOODS SIZE3-7	1-2308334-5	1-2308334-3	LOCKING SCREW (4-40 UNC LONG KNURLED)	LOCKING SCREW (4-40 UNC SHORT KNURLED)		4-40 UNC	72
1-2308342-6	FULL METAL HOODS SIZE3-6	1-2308334-6		LOCKING SCREW (M3 LONG KNURLED)		50.0	M3	75
1-2308342-5	FULL METAL HOODS SIZE3-5	1-2308334-5		LOCKING SCREW (4-40 UNC LONG KNURLED)		50.0	4-40 UNC	75
1-2308342-4	FULL METAL HOODS SIZE3-4	1-2308334-4		LOCKING SCREW (M3 SHORT KNURLED)		24.0	M3	67
1-2308342-3	FULL METAL HOODS SIZE3-3	1-2308334-3		LOCKING SCREW (4-40 UNC SHORT KNURLED)		24.0	4-40 UNC	67
1-2308342-2	FULL METAL HOODS SIZE3-2	1-2308334-2		LOCKING SCREW (M3 W/SPRING WASHER)		20.7	M3	66
1-2308342-1	FULL METAL HOODS SIZE3-1	1-2308334-1		LOCKING SCREW (4-40 UNC W/SPRING WASHER)		20.7	4-40 UNC	66
PART NO.	DESCRIPTION	SUB-PART NO.		DESCRIPTION		A	d	WEIGHT, g
PART NO. (CASE RAW)		LOCKING SCREWS						

2-2308342-6	FULL METAL HOODS SIZE3-16	1-2308334-6	1-2308334-4	LOCKING SCREW (M3 LONG KNURLED)	LOCKING SCREW (M3 SHORT KNURLED)	S OVER	M3	72
2-2308342-5	FULL METAL HOODS SIZE3-15	1-2308334-5	1-2308334-3	LOCKING SCREW (4-40 UNC LONG KNURLED)	LOCKING SCREW (4-40 UNC SHORT KNURLED)		4-40 UNC	72
2-2308342-4	FULL METAL HOODS SIZE3-14	1-2308334-6		LOCKING SCREW (M3 LONG KNURLED)		50.0	M3	75
2-2308342-3	FULL METAL HOODS SIZE3-13	1-2308334-5		LOCKING SCREW (4-40 UNC LONG KNURLED)		50.0	4-40 UNC	75
2-2308342-2	FULL METAL HOODS SIZE3-12	1-2308334-4		LOCKING SCREW (M3 SHORT KNURLED)		24.0	M3	67
2-2308342-1	FULL METAL HOODS SIZE3-11	1-2308334-3		LOCKING SCREW (4-40 UNC SHORT KNURLED)		24.0	4-40 UNC	67
2-2308342-0	FULL METAL HOODS SIZE3-10	1-2308334-2		LOCKING SCREW (M3 W/SPRING WASHER)		20.7	M3	66
1-2308342-9	FULL METAL HOODS SIZE3-9	1-2308334-1		LOCKING SCREW (4-40 UNC W/SPRING WASHER)		20.7	4-40 UNC	66
PART NO.	DESCRIPTION	SUB-PART NO.		DESCRIPTION		A	d	WEIGHT, g
PART NO. (CASE Ni-PLATED)		LOCKING SCREWS						

NOTE:

* CRIMP FLANGE PN *-2308349-* TO BE ORDERED SEPARATELY.
* CRIMP BARREL TO BE USED IN COMBINATION WITH THE FLANGE PN *-2308350-* TO BE ORDERED SEPARATELY.
* CABLE CLAMP SCREW VERSION PN *-2308272-* TO BE ORDERED SEPARATELY.



CRIMP FLANGE



CRIMP BARREL



CABLE CLAMP

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 2768-m DIN 16901 130B

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL: -

FINISH: -

DWN	KIRAN K 02AUG2016
CHK	GUNASEKHAR G 02AUG2016
APVD	GUNASEKHAR G 02AUG2016
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	

TE Connectivity

NAME: FULL METAL HOODS SIZE 3

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2308342	-

CUSTOMER DRAWING | SCALE NTS | SHEET 2 OF 2 | REV A1

2308342