EU REP
French Technology Netherlands B.V.
Strawinskylaan 3051, 1077 ZX The Hague, The Netherlands
Gebruikershandleiding
UK REP
French Technology UK Limited
Unit 1 Regent Court, Regent Road, Reading, Berkshire RG1 3EU
Gebruikershandleiding

EN

Please read this manual carefully before using the product and keep it properly.

Product Overview

This compact and portable power bank supports 30 W two-way fast charging, which can fully charge your phone in just a few hours. Its intelligent protection system can prevent over-heat, over-charge, over-discharge, high temperature, short circuit, and over-current, ensuring safe, stable, efficient, and convenient use.

Charging

This power bank supports intelligent temperature-control fast-charging technology. It automatically adjusts the charging current to ensure temperature remains at a safe level. It is recommended to use a 30 W or higher power adapter and a USB-C to USB-C cable for optimal charging speed. Please refer to the following Charge Time and Charging Capacity guide to charge the power bank. Charge Time: Approx. 2.5 hours (using a 30 W or 20 W power adapter and a USB-C to USB-C cable). Charge Capacity: Approx. 20,000 mAh (3.7 V) / 74 Wh. Low-current charge (≤ 0.5 A): When the power bank is not charging, connect it to a low-current device (≤ 0.5 A) to activate low-current charge and trickle charge. This will light up in sequence to indicate the power bank is in low-current charge mode.

The power bank will enter low-current charge mode when the battery level is below 5%. Connect it to a low-current device (≤ 0.5 A) to activate low-current charge and trickle charge. This will light up in sequence to indicate the power bank is in low-current charge mode.

Discharging

This power bank has one USB-A/USB-C port or the USB-C integrated cable for charging other devices. During discharging the battery level is indicated by the battery level indicator as follows:

Battery Level	LED1	LED2	LED3	LED4
76%–100%	Solid	Solid	Solid	Solid
51%–75%	Solid	Solid	Solid	Off
26%–50%	Solid	Solid	Off	Off
6%–25%	Solid	Off	Off	Off
0%–5%	Off	Off	Off	Off

Specifications

Model: P01S30A	Battery Type: Lithium-ion battery
Battery Energy: 74.0 Wh	Operating Temperature: 0°C to 35°C
Input: 5 V ⎓ 3 A, 9 V ⎓ 3 A, 12 V ⎓ 3 A, 15 V ⎓ 3 A, 20 V ⎓ 2.25 A (45 W Max)	
USB-C: 5 V ⎓ 3 A, 9 V ⎓ 3 A, 12 V ⎓ 3 A, 15 V ⎓ 3 A, 20 V ⎓ 2.25 A (45 W Max)	
USB-A: 5 V ⎓ 3 A, 9 V ⎓ 2 A, 12 V ⎓ 1.5 A (18 W Max)	
Output: 5 V ⎓ 3 A, 9 V ⎓ 3 A, 12 V ⎓ 3 A, 15 V ⎓ 3 A, 20 V ⎓ 2.25 A (45 W Max)	
Dimensions: 76.5 × 76.5 × 30.1 mm	

Safety Precautions

- Please fully charge the power bank on its first use.
- Use an appropriate charger and USB cable (supplied or not supplied) to charge the power bank. Do not use it to charge other devices or cars.
- Do not charge the power bank unattended when it is being charged using a charger other than the supplied one. Stop the charger and recharging when the power bank is fully charged.
- Do not charge the power bank in a high-temperature environment. Avoid exposure to direct sunlight.
- Do not charge the power bank while using it.
- The power bank supports simultaneous charging and discharging.
- Do not short-circuit, collide with, puncture, or disassemble the power bank. Do not use it if it is damaged, deformed, or leaking.
- Do not use the power bank if it is wet. Wet sources such as rain, snow, and sweat may cause damage to the internal circuitry.
- Do not use the power bank if it is overheating, emitting smoke, or has a burning smell.
- Do not use the power bank if it is swollen.
- Do not use the power bank if it is damaged by liquid.
- Do not use the power bank if it is damaged by fire.
- Do not use the power bank if it is damaged by impact.
- Do not use the power bank if it is damaged by pressure.
- Do not use the power bank if it is damaged by heat.
- Do not use the power bank if it is damaged by electricity.
- Do not use the power bank if it is damaged by chemicals.
- Do not use the power bank if it is damaged by water