

FEATURES

EXTREME IMPACT PROTECTION

Designed to withstand the rigors of the daily use in almost any environment. Meets the military standard MIL-STD 883C for I2H (4-meters).

UNINTERRUPTED POWER

Increase productivity with continuous power to the iPhone. The included 3200mAh battery pack increases the device's video playback by up to 12 hours, video streaming by up to 9 hours and audio play by back up to 45 hours.

BUILT-IN ADJUSTABLE HAND-STRAP

The hand-strap improves your grip and helps prevent the device from dropping.

TWO WAYS TO CHARGE

You can charge the Workflow Battery Case and spare battery simply by dropping it into a Workflow Charging Station, or via USB-C charging port.



TESTED & CERTIFIED
168 HRS OF MEDICAL
GRADE TESTING.



DISINFECTANTS USED IN TESTING:
 CAVICIDE
 POI SANI-CLOTH AF3
 POI SANI-CLOTH WITH BLEACH
 1 ISOPROPYL ALCOHOL SOLUTION (70%)
 1 ACTIVATED HYDROGEN PEROXIDE (0.5%)
 1 POI SUPER SANI-CLOTH (SEE INSTRUCTIONS)

The UAG Rugged Workflow Battery Case for the iPhone is equipped with a hot-swappable battery designed to keep your iPhone running 24/7. The rugged housing can handle drops up to 12-ft (4-Meters) onto concrete. Button, port and speaker covers help prevent dust and water spray from contaminating your device without inhibiting any of your device's functionality.

Rugged Battery Cases

iPhone 16 Battery Case w/ 3200mAh	Black
iPhone 16e Battery Case w/ 3200mAh	Black
iPhone 15 Battery Case w/ 3200mAh	Black
iPhone 14/13 Battery Case w/ 3200mAh	Black
iPhone 12/12 Pro Battery Case w/ 3200mAh	Black
iPhone SE / iPhone 8 Battery Case w/ 3200mAh	Black

Color

Part No.

UPC

Charging Accessories

Charge Cradle (1 case + 1 battery)
5-Slot Battery Charger
5-Slot Case Charger

Color

Part No.

UPC



SPECIFICATIONS

Case Material	Polycarbonate (PC), Thermoplastic Polyurethane (TPU)
Certification	I2B (4m)
Port & Button Protection	Covered Ports and Buttons, Accessible Lightning Port
Speaker protection	Non-Woven Mesh Acoustic Vents
Hand Strap	Adjustable, Removable
Standard Battery Pack capacity	3,200mAh Lithium Polymer, 3.7V
Battery Pack Charging input, contacts	10-Watt, 5v2A Max
Battery Pack Charging Input, USB-C	10-Watt, 5v2A Max
Battery Pack wireless charging output	5-Watt (Wireless)
Wireless Status Indicator	1x Blue LED
Battery Capacity Indicator	4x Blue LED
Weight	190 Grams (6.7oz)
Dimensions	153.4mm x 79.2mm x 24.4mm, 16in x 3.1in x 0.96in
Operating Environment	0C to +40C (32°F to 104°F) // 5% to 90% Relative Humidity
Storage Environment	-15C to +50C (-59°F to +122°F) // 5% to 90% Relative Humidity
Certifications	CE, FCC, RoHS, UN38.3, MSDS, CEC WPC010
Environmental	MIL-STD 883C
Warranty	1-Year Limited Warranty