

Smart



70°
TURN

32 - 55"
81 - 140 cm

TV size

88 lbs
max 40 kg

Max. weight

VESA

Max. 400 x 400

Height
adjustable

3 levels

Supports
Curved TV

Supports
OLED TV

Consumer benefits

Logistical information

Specifications

Version Number	WM2470-000-0001
Model name	WM2470
Product dimensions cm (LxWxH)	26x43.4x66.6
Product dimensions inch (LxWxH)	10.24x17.09x26.22
Packaging dimensions cm (LxWxH)	8.5x45.5x29.5
Packaging dimensions inch (LxWxH)	3.35x17.91x11.61
Packed product weight gross (pounds)	11.687
EAN-13 Packaging	8716184076350
Inner dimensions cm (LxWxH)	n/a
Quantity master (EA)	2
Master dimensions cm (LxWxH)	47x31.5x18.5
Master weight gross (pounds)	24.63
EAN-13 Master	8716184076367

Specifications

- Funktion: Turn
- Drehung (°): 70
- Maximales Gewicht (kg): 40
- Max weight (pounds): 88.2
- Mindestgröße (Zoll): 32
- Mindestgröße (cm): 81
- Maximale Größe (Zoll): 55
- Maximale Größe (cm): 140

Compatibility

- VESA-kompatibel
- Universal einstellbar
- Vesa-Größen: 100x100, 100x200, 200x100, 200x200, 300x200, 300x300, 400x200, 400x300, 400x400, Universally Adjustable
- Maximale Montage B (mm): 400
- Maximale Montage H (mm): 400

Features

- Height adjustable
- Kabelmanagement
- Ideal für Ecken
- Kann mit einer Schraube gesichert werden.

