

SnapLock hood/
SnapLock Haube

Cable/
Kabel

D-SUB Male 15pos./
D-SUB Stift 15pol.

Mounting material
for SnapLock/
Montagematerial
für SnapLock

Materials SnapLock hood/

Werkstoffe SnapLock Haube:

Hood/
Haube: ABS UL 94 V-0, Ni

Blanking plug/
Blindstopfen: ABS UL 94 V-0, Ni

Cable strain relief/
Zugentlastung: Steel, Ni

Clip/
Clip: Stainless Steel/
Edelstahl

Countersunk-head screw/
Linsenkopfschraube: Steel, Ni

Mounting material/
Montagematerial: Steel, Ni

Materials D-SUB Male 15pos./

Werkstoffe D-SUB Stift 15pol.:

Insulator/
Isolierkörper: PA 66 GF UL 94 V-0

Shell/
Gehäuse: Steel, Sn over Ni

Crimp contact/
Crimpkontakt: Copper alloy, Au over Ni

Contact assignment/

Kontaktbelegung:

D-Sub

1	black/schwarz
2	brown/braun
3	red/rot
4	pink/rosa
5	yellow/gelb
6	green/grün
7	blue/blau
8	violet/violett
9	grey/grau
10	white/weiss
11	grey pink/grau rosa
12	red blue/rot blau
13	white green/weiss grün
14	brown green/braun grün
15	white yellow/weiss gelb

Shielding
cable strain relief/
Schirmauflage
Zugentlastung

Part no/ Art.-Nr.:	Length L/ Länge L:	Cable/ Kabel:
16-512390	1,8 m	PVC, grey/grau, 15x0,34 mm ² , LiYCY Cable/Kabel: 781-GN31500
16-512400	3 m	
16-512410	5 m	

tolerance of cable/ <i>Kabeltoleranz:</i>		L ≤ 4 m; L + 40 mm L > 4 m; L + 1 %				dim. in mm	
general tolerance/ <i>Allgemeintoleranz:</i>		0 ± 0,50 mm		Date/ <i>Datum</i>		Name	
		0,0 ± 0,25 mm		drawn/ gez.		26.11.2024 Lehmenkühler	
		0,00 ± 0,10 mm ≤ 5°		appd./ gepr.		02.12.2024 Koch	
Index: b 09.04.2025 JLE		scale/ <i>Maßstab:</i> 2:1					

D-Sub Male 15pol. in SnapLock hood
with cable and mounting material
D-SUB Stift 15pol. in SnapLock Haube
mit Kabel und Befestigungsmaterial

dwg no /
Z.-nr.: 16K1A4395

DIN-
A3

Customer specific product

1 / 1