





“Schutzvermerk nach DIN ISO 16016 beachten” “Please pay attention to copyright note DIN ISO 16016”




A-A (1 : 1)




ISO (1 : 1)





B-B (1 : 1)




Oberteil
Lid




C-C (1 : 1)



Z (2 : 1)



Y (2 : 1)



Für Version mit Einlegedichtung:

Schutzart IP40. Um Schutzart IP65 zu erreichen, muss die beiliegende Dichtung korrekt montiert werden. Die Dichtung darf in den Ecken weder gestreckt noch gestaucht werden. Stoßstelle schräg geschnitten und verklebt, sodaß die Schnittstellen durch den Federdruck aufeinander gedrückt werden.

For Version with enclosed gasket

Protection class IP40. To achieve protection class IP65, the enclosed gasket must be mounted correctly. The gasket must not be stretched or compressed in the corners. Ends cut obliquely and glued, so that the cut ends are pressed together by the spring pressure.

BOX^{4U}		Zeichnungs-Nr. / Drawing-No.: 2K 5455.104.01	
		6U-090906	
Datum/Date 28.01.2025		Name/name MG	
Gezeichnet		Katalogzg./Catalogue draw.	
Kontrolliert		2504974.idw	
Norm		A2	
Status	Ä.Nr./Alt.No	Datum/Date	Name