

Glassockellampen, T10

Socket W2,1x9,5d

(10x27mm)



Spannung	Strom	Leistung	Artikel-Nr.
6,3V	150mA	1W	00570615
6-7V	333mA	2W	00570602
12V	100mA	1,2W	00571212
	250mA	3W	00571203
	420mA	5W	00571205
12-15V	166mA	2W	00571202
24-30V	83mA	2W	00572402
48-60V	33mA	2W	00574802
Lampenzieher T3¼			01909007

Glassockellampen, T15

Socket W2,1x9,5d

(15x36mm)



Spannung	Strom	Leistung	Artikel-Nr.
12V	400mA	5W	00575126
	600mA	7W	00575127
	670mA	8W	00575129
	830mA	10W	00575121
	1,25A	15W	00575122
	1,66A	20W	00575123
24V	210mA	5W	00575245

Rigid-Loop Xenon-Lampen

(10x44mm)



Spannung	Leistung	Ausführung	Artikel-Nr.
12V	5W	klar	10701205
	5W	matt	10711205
	8,5W	klar	10701285
	10W	matt	10711210
24V	5W	klar	10702405
	5W	matt	10712405

