V-TAC
Meaningful Innovation.

PRODUCT SPEC SHEET

SKU 211976 Model:VT-227D EAN:3800170240797

VT-227D 6W GU10 RIPPLE PLASTIC SPOTLIGHT CREE CHIP 6500K 38'D DIMMABLE 6YRS WTY



A↑G F | IP20 STANDARD | 6 YEAR WARRANTY | CREE LED POWERED

- New Range of GU10 Spotlights with SMD-CREE Chip technology for better reliability
- Lasts 25,000 Hours, longer life span than Standard halogen spotlights
- Replaces 60 watts old halogen lamp
- Easy to install, designed with GU10 base
- Built with dimming feature
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

TECHNICAL INFORMATION

Dimmable:	Yes
On/Off Cycles:	>20000
Model:	VT-227D
Color Temperature:	6500K
CRI:	>80
Watts:	6
Lumens:	445
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	60
Unit Color:	White
Color for Web:	White
Body Type:	Plastic
Dimension:	50x55mm

LISTING DETAILS

SKU:	211976
Model:	VT-227D
EAN:	3800170240797
Commodity Code:	8539521000

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000234
Dimension:	50x55mm

MASTER BOX PACKAGING

Box Qty:	200
Qty Per Pallet:	

Operation Temperature:	-20°C to +45°C
Base:	GU10
LED Chip Type:	SMD-CREE Chip
Beam Angle:	38°
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
IP Rating:	IP20
Long Life:	25,000 Hours

Length (Box) mm:	50
Width (Box) mm:	50
Height (Box) mm:	80