



PRODUCT SPEC SHEET

SKU 203476

Model:VT-8-20

EAN:3800170241046

VT-8-20 20W LED GRILL FITTING 566MM CREE CHIP 3000K 6YRS WTY 100LM/W



IP20
STANDARD



- Prismatic Fitting designed with Lumen efficiency 100LM/W
- Fitted with high efficiency SMD-CREE Chip that offer up to 85% in energy savings
- Quick Connector for easy installation
- 50% less power consumption compared to traditional grill fitting lighting
- Switch cycles: >15000
- Instant start-up in less than 1 second
- Applications - Residential, Hotels, Malls, Office and many more

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>15000
Instant Start:	0-100% in <1s
Model:	VT-8-20
Color Temperature:	3000K
CRI:	>80
Watts:	20
Lumens:	2050
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	Warm White
Body Type:	Plastic
Dimension:	566x76x24mm
Operation Temperature:	-20°C to +40°C

LISTING DETAILS

SKU:	203476
Model:	VT-8-20
EAN:	3800170241046
Commodity Code:	9405110000

PACKAGING

Gross Weight (Kgs):	0.24
Unit CBM:	0.001804
Dimension:	566x76x24mm

MASTER BOX PACKAGING

Box Qty:	30
Qty Per Pallet:	
Length (Box) mm:	80

PF:	>0.7
LED Chip Type:	SMD-CREE Chip
Beam Angle:	120°
Energy Rating Label:	F (2021)
Energy Saving:	85 Energy
IP Rating:	IP20
IK Rating:	IK06
Long Life:	30,000 Hours
lumens per watt:	100

Width (Box) mm:	30
Height (Box) mm:	605